

PRODUCT-DETAILS

ACH580-01-430A-4+B056

LV AC wall-mounted drive for HVAC, IEC: Pn 250 kW, 430 A, 400 V, UL: Pld 350 Hp, 414 A (ACH580-01-430A-4+B056)



General Information

Global Commercial Alias	ACH580-01-430A-4+B056
Product ID	3AUA0000083610
ABB Type Designation	ACH580-01-430A-4+B056
EAN	6438177306412
Catalog Description	LV AC wall-mounted drive for HVAC, IEC: Pn 250 kW, 430 A, 400 V, UL: Pld 350 Hp, 414 A (ACH580-01-430A-4+B056)
Long Description	ACH580 HVAC drive offering has all key features built-in to control fans, pumps and compressors, and more complex equipment like air-handling units and chillers, ensuring smooth, energy-efficient operation of your HVAC systems in normal and mission-critical situations. The built-in features significantly reduce installation time and the intuitive control panel with an HVAC-specific primary settings menu and help assistants makes startup, commissioning and operation easy. The optional Bluetooth® capability enables the commissioning and monitoring of the drive from a distance. The ACH580-01 comes in IP21 enclosure and can be installed on the wall as standard. Also, IP55 and flange mounting units are available.

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044086
Invoice Description	ACH580-01-430A-4+B056 PN: 250 kW, IN: 430 A
Made To Order	Yes
Minimum Order Quantity	1 piece

Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	173.103 dm³
--------------	-------------

Dimensions

Product Net Weight	103 kg 227.076 lb
Product Net Depth / Length	477.00 mm 18.780 in
Product Net Height	955.00 mm 37.598 in
Product Net Width	380.00 mm 14.961 in
Package Level 1 Depth / Length	1145.00 mm 45.079 in
Package Level 1 Height	630.00 mm 24.803 in
Package Level 1 Width	485.00 mm 19.094 in
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP55
Enclosure Type NEMA	Type12
	95
Multiple Battery Information	Lithium Coin, CR2032, 220 mAh, 3 V, 1 pc, 3 g
Frequency (f)	47.5 ... 63 Hz
Frame Size	R9
Input Voltage (U _{in})	380 ... 480 V
Communication Protocol	BACNET CAN DeviceNet EtherNet/IP LON MODBUS Other Bus Systems PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Other 2 Parallel 2 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	With control unit Without optical interface With PC connection

Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	6/3
Output Current, Heavy-Duty Use (I_{HD})	363 A
Output Current, Light-Overload Use (I_{LD})	400 A
Output Current, Normal Use (I_n)	430 A
Output Power, Heavy-Duty Use (P_{HD})	200 kW
Output Power, Light-Overload Use (P_{LD})	200 kW
Output Power, Normal Use (P_n)	250 kW
Apparent Power Output	298 kV·A
Efficiency Level	IE2
Standby Loss	80 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Efficiency	Relative Loss
0/25 %	1471 W	91.5 %	0.5 %
0/50 %	2121 W	93.6 %	0.7 %
0/100 %	4032 W	93.9 %	1.4 %
50/25 %	1615 W	95.4 %	0.5 %
50/50 %	2393 W	96.5 %	0.8 %
50/100 %	4676 W	96.5 %	1.6 %
90/50 %	2821 W	97.6 %	0.9 %
90/100 %	6072 W	97.5 %	2.0 %

Temperature Rating	Maximum 40 °C Minimum -15 °C
--------------------	---------------------------------

Additional Information

Product Main Type	ACH580-01
Product Name	Frequency converter

Classifications

ETIM 8	EC001857 - Frequency converter =< 1 kV
ETIM 9	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

Environmental

SCIP	d18b6fc2-582d-43fe-991a-760f8051bde1 Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-01 - Wall-mounted drive for HVAC

