

## PRODUCT-DETAILS

# ACS880-07-0105A-3

## ACS880-07-0105A-3 PN: 55 kW, IN: 105 A



### General Information

Global Commercial Alias	ACS880-07-0105A-3
Product ID	3AUA0000120564
ABB Type Designation	ACS880-07-0105A-3
Catalog Description	ACS880-07-0105A-3 PN: 55 kW, IN: 105 A

### Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044086
Invoice Description	ACS880-07-0105A-3 PN: 55 kW, IN: 105 A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

### Dimensions

Product Net Weight	240 kg 529 lb
Product Net Depth / Length	673 mm 26.50 in

Product Net Height	2145 mm 84.45 in
Product Net Width	430 mm 16.93 in
Package Level 1 Depth / Length	1100 mm 43.31 in
Package Level 1 Height	2385 mm 93.90 in
Package Level 1 Width	1144 mm 45.04 in

<b>Technical</b>	
Number of Phases	3
Degree of Protection	IP22
Enclosure Type NEMA	Type1
Altitude	1000 m
	5 ... 95
Power Factor	0.98
Sound dB (A)	67 dB(A)
Multiple Battery Information	Lithium Coin, CR2032, 2pcs, 3V, 220mAh, 6g
Frequency (f)	48 ... 63 Hz
Frame Size	R6
Input Voltage ( $U_{in}$ )	380 ... 415 V
Mounting Type	Cabinet-built
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIsafe PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Parallel 0 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	Control unit PC connection
Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	7 / 5
Output Current, Heavy-Duty Use ( $I_{HD}$ )	87 A
Output Current, Light-Overload Use ( $I_{LD}$ )	100 A
Output Current, Normal Use ( $I_n$ )	105 A
Output Power, Heavy-Duty Use ( $P_{HD}$ )	45 kW
Output Power, Light-Overload Use ( $P_{LD}$ )	55 kW
Output Power, Normal Use ( $P_n$ )	55 kW

Apparent Power Output	73 kV·A
Standby Loss	102 W
Complete Drive Module	
Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Efficiency	Relative Loss
0/25 %	450 W	89.8 %	0.6 %
0/50 %	565 W	93.1 %	0.8 %
0/100 %	887 W	94.4 %	1.2 %
50/25 %	485 W	94.4 %	0.7 %
50/50 %	632 W	96.2 %	0.9 %
50/100 %	1027 W	96.8 %	1.4 %
90/50 %	726 W	97.5 %	1.0 %
90/100 %	1315 W	97.7 %	1.8 %

Temperature Rating	Maximum 40 °C Minimum 0 °C
Ecodesign Exemption	Energy efficiency data is not provided for this cabinet-built drive. Cabinet-built drives, with already conform modules, are excluded from the scope of the EU ecodesign requirements (Regulation EU/2019/1781, §2.3.e).

Additional Information

Product Main Type	ACS880-07
Product Name	Frequency converter

Classifications

UNSPSC	39122001
--------	----------

Environmental

SCIP	e1aec134-b168-4e21-9c40-ee5e90c4bab4 Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 single drives → ACS880-07 - Cabinet-built single drive

