

PRODUCT-DETAILS

ACS880-07-0522A-7

ACS880-07-0522A-7 PN: 500 kW, IN: 522 A



General Information

Global Commercial Alias	ACS880-07-0522A-7
Product ID	3AUA0000154957
ABB Type Designation	ACS880-07-0522A-7
Catalog Description	ACS880-07-0522A-7 PN: 500 kW, IN: 522 A

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044086
Invoice Description	ACS880-07-0522A-7 PN: 500 kW, IN: 522 A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	580 kg 1279 lb
--------------------	-------------------

Product Net Depth / Length	698 mm 27.48 in
Product Net Height	2145 mm 84.45 in
Product Net Width	830 mm 32.68 in
Package Level 1 Depth / Length	1100 mm 43.31 in
Package Level 1 Height	2385 mm 93.90 in
Package Level 1 Width	1144 mm 45.04 in

Technical

Number of Phases	3
Degree of Protection	IP22
Enclosure Type NEMA	Type1
Altitude	1000 m
	5 ... 95
Power Factor	0.98
Sound dB (A)	72 dB(A)
Multiple Battery Information	Lithium Coin, CR2032, 2pcs, 3V, 220mAh, 6g
Frequency (f)	48 ... 63 Hz
Frame Size	R11
Input Voltage (U_{in})	525 ... 690 V
Mounting Type	Cabinet-built
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIsafe PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Parallel 0 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	Control unit PC connection
Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	7 / 5
Output Current, Heavy-Duty Use (I_{HD})	455 A
Output Current, Light-Overload Use (I_{LD})	505 A
Output Current, Normal Use (I_n)	522 A
Output Power, Heavy-	450 kW

Duty Use (P_{HD})	
Output Power, Light-	500 kW
Overload Use (P_{LD})	
Output Power, Normal	500 kW
Use (P_n)	
Apparent Power Output	624 kV-A
Standby Loss	438 W
Complete Drive Module	
Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Efficiency	Relative Loss
0/25 %	2569 W	92.8 %	0.4 %
0/50 %	3503 W	94.9 %	0.6 %
0/100 %	5560 W	95.9 %	0.9 %
50/25 %	2774 W	96.2 %	0.4 %
50/50 %	3883 W	97.2 %	0.6 %
50/100 %	6431 W	97.7 %	1.0 %
90/50 %	4402 W	98.2 %	0.7 %
90/100 %	7578 W	98.5 %	1.2 %

Temperature Rating	Maximum 40 °C Minimum 0 °C
Ecodesign Exemption	Energy efficiency data is not provided for this cabinet-built drive. Cabinet-built drives, with already conform modules, are excluded from the scope of the EU ecodesign requirements (Regulation EU/2019/1781, §2.3.e).

Additional Information	
Product Main Type	ACS880-07
Product Name	Frequency converter

Classifications	
UNSPSC	39122001

Environmental	
SCIP	e1aec134-b168-4e21-9c40-ee5e90c4bab4 Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 single drives → ACS880-07 - Cabinet-built single drive

