



PRODUCT-DETAILS

ACQ580-01-06A0-4+B056

LV AC wall-mounted drive for water and wastewater, UL: Pld 3.0 Hp, 6.0 A, 440 ... 480 V (ACQ580-01-06A0-4+B056)

General Information

Global Commercial Alias	ACQ580-01-06A0-4+B056
Product ID	3AUA0000204877
ABB Type Designation	ACQ580-01-06A0-4+B056
EAN	6438177451365
Catalog Description	LV AC wall-mounted drive for water and wastewater, UL: Pld 3.0 Hp, 6.0 A, 440 ... 480 V (ACQ580-01-06A0-4+B056)

Long Description	The ACQ580-01 drives deliver innovative pump features for the water and wastewater industry, securing energy efficient flow of water and wastewater in your pumping solutions. This robust and compact wall-mounted drive has built-in pump application functionality such as sensorless flow calculation, multipump control, level control, soft pipe fill, dry run protection, quick ramps and a solution for keeping the impeller of the pump clean. Usability is further enhanced with the intuitive Hand-Off-Auto control panel, the PC tool Drive composer and an optional Bluetooth® control panel. The built-in energy calculator visualizes the energy savings achieved with the use of the drive. The ACQ580-01 variant comes in IP21 enclosure as standard and can be installed on the wall. Also, IP55 and flange mounting units are available.
------------------	---

Ordering

Country of Origin	Finland (FI) Romania (RO)
Customs Tariff Number	85044080
Invoice Description	ACQ580-01-06A0-4+B056, PLD 3 HP, I2LD 6.0 A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	11 lb
Product Net Depth / Length	9.17 in
Product Net Height	15.86 in
Product Net Width	5.06 in
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP55
Enclosure Type NEMA	Type12
Frequency (f)	50/60 Hz
Frame Size	R1
Input Voltage (U _{in})	440 ... 480 V
Mounting Type	Wall-mounting
Apparent Power Output	5.0 kV·A
Efficiency Level	IE2
Standby Loss	15 W
Complete Drive Module	
Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	45 W	0.9 %	85.6 %
0 / 50 %	51 W	1.0 %	91.0 %
0 / 100 %	66 W	1.3 %	93.5 %
50 / 25 %	46 W	0.9 %	92.2 %
50 / 50 %	54 W	1.1 %	95.2 %
50 / 100 %	72 W	1.5 %	96.5 %
90 / 50 %	58 W	1.2 %	97.1 %
90 / 100 %	81 W	1.6 %	97.8 %

Temperature Rating	Maximum 40 °C
--------------------	---------------

Additional Information

Product Name	AC Drive
--------------	----------

Classifications

UNSPSC	39122001
--------	----------

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for water → ACQ580-01 - Wall-mounted drive for water and wastewater