



## PRODUCT-DETAILS

# ACQ580-01-078A-4+B056

## LV AC wall-mounted drive for water and wastewater, UL: Pld 60 Hp, 77 A, 460 V (ACQ580-01-078A-4+B056)

### General Information

Global Commercial Alias	ACQ580-01-078A-4+B056
Product ID	3AUA0000222429
ABB Type Designation	ACQ580-01-078A-4+B056
EAN	6438177508120
Catalog Description	LV AC wall-mounted drive for water and wastewater, UL: Pld 60 Hp, 77 A, 460 V (ACQ580-01-078A-4+B056)

Long Description	The ACQ580-01 drives deliver innovative pump features for the water and wastewater industry, securing energy efficient flow of water and wastewater in your pumping solutions. This robust and compact wall-mounted drive has built-in pump application functionality such as sensorless flow calculation, multipump control, level control, soft pipe fill, dry run protection, quick ramps and a solution for keeping the impeller of the pump clean. Usability is further enhanced with the intuitive Hand-Off-Auto control panel, the PC tool Drive composer and an optional Bluetooth® control panel. The built-in energy calculator visualizes the energy savings achieved with the use of the drive. The ACQ580-01 variant comes in IP21 enclosure as standard and can be installed on the wall. Also, IP55 and flange mounting units are available.
------------------	---

### Ordering

Country of Origin	Finland (FI) United States (US)
Customs Tariff Number	85044080
Invoice Description	ACQ580-01-078A-4+B056, PLD 60 HP, I2LD 78 A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

### Dimensions

Product Net Weight	64 lb
Product Net Depth / Length	12.59 in
Product Net Height	28.83 in
Product Net Width	7.99 in
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP55
Enclosure Type NEMA	Type12
Frequency (f)	50/60 Hz
Frame Size	R5
Input Voltage (U <sub>in</sub> )	440 ... 480 V
Mounting Type	Wall-mounting
Apparent Power Output	64 kV·A
Efficiency Level	IE2
Standby Loss	24 W
Complete Drive Module	
Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	266 W	0.4 %	92.9 %
0 / 50 %	354 W	0.6 %	95.0 %
0 / 100 %	648 W	1.0 %	95.3 %
50 / 25 %	291 W	0.5 %	96.1 %
50 / 50 %	407 W	0.6 %	97.2 %
50 / 100 %	766 W	1.2 %	97.3 %
90 / 50 %	465 W	0.7 %	98.2 %
90 / 100 %	941 W	1.5 %	98.1 %

Temperature Rating	Maximum 40 °C
--------------------	---------------

Additional Information

Product Name	AC Drive
--------------	----------

Classifications

UNSPSC	39122001
--------	----------

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
---------------	---

---

## Categories

---

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for water → ACQ580-01 - Wall-mounted drive for water and wastewater