

PRODUCT-DETAILS

ACS880-01-09A8-3+N7502

ACS880-01-09A8-3+N7502 PN: 4.0 kW, IN: 9.8 A



General Information

Global Commercial Alias	ACS880-01-09A8-3+N7502
Product ID	3AXD50000035914
ABB Type Designation	ACS880-01-09A8-3+N7502
Catalog Description	ACS880-01-09A8-3+N7502 PN: 4.0 kW, IN: 9.8 A

The ACS880-01 drives are customized to meet the particular needs of specific industries, such as oil and gas, mining, metals, chemicals, cement, power plants, material handling, pulp and paper, sawmills, marine, water and wastewater, food and beverage, and automotive. They can control a wide range of applications, including cranes, extruders, winches, winders, conveyors, mixers, compressors, centrifuges, test benches, elevators, extruders, pumps and fans.

Long Description

The ACS880-01 comes in one compact package for easy installation and commissioning. The drive can be installed on the wall as standard and in a cabinet as an option. The drive offering includes enclosure classes up to IP55, making it suitable for most environments and installations. ACS880-01 drives have all the essential features built-in. These features include as standard a choke for harmonic filtering as well as options like a brake chopper, EMC filter and communication protocol adapter, functional safety, external output filters and I/O extension modules.

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044086
Invoice Description	ACS880-01-09A8-3+N7502 PN: 4.0 kW, IN: 9.8 A

Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	7.0 kg 15.432 lb
Product Net Depth / Length	226 mm 8.898 in
Product Net Height	409 mm
Product Net Width	155 mm 6.102 in
Package Level 1 Depth / Length	570 mm
Package Level 1 Height	280 mm
Package Level 1 Width	260 mm
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Multiple Battery Information	Lithium Coin, CR2032, 220 mAh, 3 V, 2 pcs, 6 g
Frequency (f)	47.5 ... 63 Hz
Frame Size	R1
Input Voltage (U _{in})	380 ... 415 V
Mounting Type	Wall-mounted
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIsafe PROFIBUS PROFINET IO
Number of Hardware Interfaces	Industrial Ethernet 0 Other 4 Parallel 0 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	Control unit PC connection
Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	6 / 2
Output Current, Heavy-Duty Use (I _{HD})	7.5 A
Output Current, Light-	9.8 A

Overload Use (I_{LD})	
Output Current, Normal	9.8 A
Use (I_n)	
Output Power, Heavy-	3 kW
Duty Use (P_{HD})	
Output Power, Light-	4 kW
Overload Use (P_{LD})	
Output Power, Normal	4 kW
Use (P_n)	
Apparent Power Output	6.8 kV-A
Efficiency Level	IE2
Standby Loss	23 W
Complete Drive Module	
Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	66 W	1.0 %	84.5 %
0 / 50 %	79 W	1.2 %	89.7 %
0 / 100 %	114 W	1.7 %	91.9 %
50 / 25 %	69 W	1.0 %	91.5 %
50 / 50 %	86 W	1.3 %	94.4 %
50 / 100 %	129 W	1.9 %	95.4 %
90 / 50 %	96 W	1.4 %	96.5 %
90 / 100 %	151 W	2.2 %	97.0 %

Temperature Rating	Maximum 40 °C
--------------------	---------------

Additional Information

Product Main Type	ACS880-01
Product Name	Frequency converter

Classifications

ETIM 8	EC001857 - Frequency converter =< 1 kV
ETIM 9	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 single drives → ACS880-01 - Wall-mounted single drive

