

PRODUCT-DETAILS

ACQ580-01-293A-4+B056

LV AC wall-mounted drive for water and wastewater, IEC: Pn 160 kW, 293 A (ACQ580-01-293A-4+B056)



General Information

Global Commercial Alias	ACQ580-01-293A-4+B056
Product ID	3AXD50000034630
ABB Type Designation	ACQ580-01-293A-4+B056
EAN	6438177410164

Catalog Description	LV AC wall-mounted drive for water and wastewater, IEC: Pn 160 kW, 293 A (ACQ580-01-293A-4+B056)
---------------------	--

The ACQ580-01 drives deliver innovative pump features for the water and wastewater industry, securing energy efficient flow of water and wastewater in your pumping solutions. This robust and compact wall-mounted drive has built-in pump application functionality such as sensorless flow calculation, multipump control, level control, soft pipe fill, dry run protection, quick ramps and a solution for keeping the impeller of the pump clean.

Long Description

Usability is further enhanced with the intuitive Hand-Off-Auto control panel, the PC tool Drive composer and an optional Bluetooth® control panel. The built-in energy calculator visualizes the energy savings achieved with the use of the drive. The ACQ580-01 variant comes in IP21 enclosure as standard and can be installed on the wall. Also, IP55 and flange mounting units are available.

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044085
Invoice Description	ACQ580-01-293A-4+B056 PN: 160 kW, IN: 293 A

Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	130.854 dm³
--------------	-------------

Dimensions

Product Net Weight	77 kg 169.756 lb
Product Net Depth / Length	452.00 mm 17.795 in
Product Net Height	965.00 mm 37.992 in
Product Net Width	300.00 mm 11.811 in
Package Level 1 Depth / Length	1145.00 mm 45.079 in
Package Level 1 Height	630.00 mm 24.803 in
Package Level 1 Width	485.00 mm 19.094 in
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP55
Enclosure Type NEMA	Type12
	95
Multiple Battery Information	Lithium Coin, CR2032, 220 mAh, 3 V, 1 pc, 3 g
Frequency (f)	47.5 ... 63 Hz
Frame Size	R8
Input Voltage (U _{in})	380 ... 480 V
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Other 2 Parallel 2 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	With control unit Without optical interface

	With PC connection
Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	6 / 3
Output Current, Heavy-Duty Use (I_{HD})	246 A
Output Current, Light-Overload Use (I_{LD})	278 A
Output Current, Normal Use (I_n)	293 A
Output Power, Heavy-Duty Use (P_{HD})	132 kW
Output Power, Light-Overload Use (P_{LD})	160 kW
Output Power, Normal Use (P_n)	160 kW
Apparent Power Output	203 kV·A
Efficiency Level	IE2
Standby Loss	47 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Efficiency	Relative Loss
0/25 %	981 W	91.8 %	0.5 %
0/50 %	1382 W	93.9 %	0.7 %
0/100 %	2541 W	94.3 %	1.3 %
50/25 %	1088 W	95.5 %	0.5 %
50/50 %	1582 W	96.5 %	0.8 %
50/100 %	3032 W	96.6 %	1.5 %
90/50 %	1907 W	97.7 %	0.9 %
90/100 %	4071 W	97.5 %	2.0 %

Temperature Rating	Maximum 40 °C Minimum -15 °C
--------------------	---------------------------------

Additional Information

Product Main Type	ACQ580-01
Product Name	Frequency converter

Classifications

ETIM 8	EC001857 - Frequency converter =< 1 kV
ETIM 9	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

Environmental

SCIP	1b7d3fcb-8dfc-4964-9a9a-bec89b35caf1 Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for water → ACQ580-01 - Wall-mounted drive for water and wastewater

