

PRODUCT-DETAILS

ACS580-01-033A-4+B056

LV AC general purpose wall-mounted drive,
IEC: Pn 15 kW, 32 A, 400 V, 480 V (ACS580-01-033A-4+B056)



General Information

Global Commercial Alias	ACS580-01-033A-4+B056
Product ID	3AXD50000038978
ABB Type Designation	ACS580-01-033A-4+B056
EAN	6438177459385
Catalog Description	LV AC general purpose wall-mounted drive, IEC: Pn 15 kW, 32 A, 400 V, 480 V (ACS580-01-033A-4+B056)

The ACS580-01 is plug-in ready to control your compressors, conveyors, pumps, extruders, centrifuges, mixers, fans and many other variable and constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture.

Long Description

All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. Versatile and straightforward settings menu and assistants enable fast setup, commissioning, use and maintenance, while rugged and robust design makes it a good fit for various environments. With the ACS580 drives you can easily take full control of your processes to comprehensively manage your plant. The wall-mounted ACS580-01 comes in IP21 enclosure as standard. Also, IP55 and flange mounting units are available.

Ordering

Country of Origin	Romania (RO) Finland (FI) China (CN)
-------------------	--

Customs Tariff Number	85044085
Invoice Description	ACS580-01-033A-4+B056 PN: 15.0 kW, IN: 32 A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	23.923 dm³
--------------	------------

Dimensions

Product Net Weight	13 kg 28.660 lb
Product Net Depth / Length	237.00 mm 9.331 in
Product Net Height	490.00 mm 19.291 in
Product Net Width	206.00 mm 8.110 in
Package Level 1 Depth / Length	295.00 mm 11.614 in
Package Level 1 Height	390.00 mm 15.354 in
Package Level 1 Width	600.00 mm 23.622 in
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP55
Enclosure Type NEMA	Type12
Altitude	1000 m 95
Sound dB (A)	76 dB(A)
Multiple Battery Information	Lithium Coin, CR2032, 220 mAh, 3 V, 1 pc, 3 g
Frequency (f)	47.5 ... 63 Hz
Frame Size	R3
Input Voltage (U _{in})	380 ... 480 V
Mounting Type	Wall-mounted
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Other 2 Parallel 2 PROFINET 0

	RS-232 0
	RS-422 0
	RS-485 1
	Serial TTY 0
	USB 1
Includes	Control unit PC connection
Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	6 / 3
Output Current, Heavy-Duty Use (I_{HD})	24.6 A
Output Current, Light-Overload Use (I_{LD})	30.4 A
Output Current, Normal Use (I_n)	32 A
Output Power, Heavy-Duty Use (P_{HD})	11.0 kW
Output Power, Light-Overload Use (P_{LD})	15.0 kW
Output Power, Normal Use (P_n)	15 kW
Apparent Power Output	22 kV-A
Efficiency Level	IE2
Standby Loss	16 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Efficiency	Relative Loss
0/25 %	162 W	87.8 %	0.7 %
0/50 %	205 W	91.7 %	0.9 %
0/100 %	351 W	92.8 %	1.6 %
50/25 %	175 W	93.3 %	0.8 %
50/50 %	228 W	95.4 %	1.0 %
50/100 %	404 W	95.9 %	1.8 %
90/50 %	252 W	97.1 %	1.1 %
90/100 %	492 W	97.2 %	2.2 %

Temperature Rating	Maximum 50 °C Minimum -15 °C
--------------------	---------------------------------

Additional Information	
Product Main Type	ACS580-01
Product Name	Frequency converter

Classifications	
ETIM 8	EC001857 - Frequency converter =< 1 kV
ETIM 9	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

Environmental

SCIP	7ab39eb4-9330-424a-b7ff-fcf491eb4b83 Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → General Purpose Drives → ACS580-01 - Wall-mounted drive

