



PRODUCT-DETAILS

ACS880-17-0361A-5

ACS880-17-0361A-5; ACS880-17-0361A-5 PN:
200 kW, IN: 361 A

General Information

Global Commercial Alias	ACS880-17-0361A-5
Product ID	3AXD50000042656
ABB Type Designation	ACS880-17-0361A-5
Catalog Description	ACS880-17-0361A-5; ACS880-17-0361A-5 PN: 200 kW, IN: 361 A

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044085
Invoice Description	ACS880-17-0361A-5 PN: 200 kW, IN: 361 A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	750 kg 1653 lb
Product Net Depth / Length	698 mm 27.48 in
Product Net Height	2145 mm 84.45 in
Product Net Width	1230 mm 48.43 in
Package Level 1 Depth / Length	1100 mm 43.31 in
Package Level 1 Height	2373 mm 93.43 in
Package Level 1 Width	1444 mm 56.85 in

Technical

Number of Phases	3
------------------	---

Degree of Protection	IP22
Enclosure Type NEMA	Type1
Altitude	1000 m
	5 ... 95
Power Factor	1
Sound dB (A)	77 dB(A)
Multiple Battery Information	Lithium Coin, CR2032, 2pcs, 3V, 220mAh, 6g
Frequency (f)	48 ... 63 Hz
Frame Size	R11
Input Voltage (U_{in})	380 ... 500 V
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIsafe PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Parallel 0 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	Control unit PC connection
Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	7 / 5
Output Current, Heavy-Duty Use (I_{HD})	260 A
Output Current, Light-Overload Use (I_{LD})	343 A
Output Current, Normal Use (I_n)	361 A
Output Power, Heavy-Duty Use (P_{HD})	160 kW
Output Power, Light-Overload Use (P_{LD})	200 kW
Output Power, Normal Use (P_n)	200 kW
Apparent Power Output Complete Drive Module Efficiency (61800-9-2)	313 kV-A

Operating Point Frequency / Current		
	0/25 %	
	0/50 %	
	0/100 %	
	50/25 %	
	50/50 %	
	50/100 %	
	90/50 %	
	90/100 %	
Temperature Rating	Maximum 40 °C Minimum 0 °C	
Ecodesign Exemption	Energy efficiency data is not provided for the drive. The regenerative drives are exempt from the EU ecodesign requirements (Regulation EU/2019/1781, §2.3.c).	

Additional Information		
Product Main Type	ACS880-17	
Product Name	Frequency converter	

Classifications		
UNSPSC	39122001	

Environmental		
SCIP	82D82DAE-9725-4373-865D-AA949B97DE50 Finland (FI)	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)	

Categories		
Drives → Low Voltage AC Drives → Industrial Drives → ACS880 single drives → ACS880-17 - Cabinet-built regenerative single drive		
Drives → Services → Spares and Consumables → Parts		