

PRODUCT-DETAILS

# ACH580-01-03A4-4+B056

LV AC wall-mounted drive for HVAC, IEC: Pn 1.1 kW, 3.3 A, 400 V, UL: Pld 1.5 Hp, 3.0 A (ACH580-01-03A4-4+B056)



## General Information

Global Commercial Alias	ACH580-01-03A4-4+B056
Product ID	3AXD50000038999
ABB Type Designation	ACH580-01-03A4-4+B056
EAN	6438177459545
Catalog Description	LV AC wall-mounted drive for HVAC, IEC: Pn 1.1 kW, 3.3 A, 400 V, UL: Pld 1.5 Hp, 3.0 A (ACH580-01-03A4-4+B056)
Long Description	ACH580 HVAC drive offering has all key features built-in to control fans, pumps and compressors, and more complex equipment like air-handling units and chillers, ensuring smooth, energy-efficient operation of your HVAC systems in normal and mission-critical situations. The built-in features significantly reduce installation time and the intuitive control panel with an HVAC-specific primary settings menu and help assistants makes startup, commissioning and operation easy. The optional Bluetooth® capability enables the commissioning and monitoring of the drive from a distance. The ACH580-01 comes in IP21 enclosure and can be installed on the wall as standard. Also, IP55 and flange mounting units are available.

## Ordering

Country of Origin	Romania (RO) Finland (FI) China (CN)
Customs Tariff Number	85044085
Invoice Description	ACH580-01-03A4-4+B056 PN: 1.1 kW, IN: 3.3 A

Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	12.019 dm³
--------------	------------

Dimensions

Product Net Weight	4.8 kg 10.582 lb
Product Net Depth / Length	233.00 mm 9.173 in
Product Net Height	403 mm 15.866 in
Product Net Width	128.00 mm 5.039 in
Package Level 1 Depth / Length	225.00 mm 8.858 in
Package Level 1 Height	370.00 mm 14.567 in
Package Level 1 Width	526.00 mm 20.709 in
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP55
Enclosure Type NEMA	Type12
	95
Multiple Battery Information	Lithium Coin, CR2032, 220 mAh, 3 V, 1 pc, 3 g
Frequency (f)	47.5 ... 63 Hz
Frame Size	R1
Input Voltage (U <sub>in</sub> )	380 ... 480 V
Communication Protocol	BACNET CAN DeviceNet EtherNet/IP LON MODBUS Other Bus Systems PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Other 2 Parallel 2 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1

Includes

With control unit  
Without optical interface  
With PC connection

Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	6/3
Output Current, Heavy-Duty Use ( $I_{HD}$ )	2.6 A
Output Current, Light-Overload Use ( $I_{LD}$ )	3.1 A
Output Current, Normal Use ( $I_N$ )	3.3 A
Output Power, Heavy-Duty Use ( $P_{HD}$ )	0.8 kW
Output Power, Light-Overload Use ( $P_{LD}$ )	1.1 kW
Output Power, Normal Use ( $P_N$ )	1.1 kW
Apparent Power Output	2.3 kV-A
Efficiency Level	IE2
Standby Loss	14 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Efficiency	Relative Loss
0/25 %	32 W	79.2 %	1.4 %
0/50 %	34 W	87.2 %	1.5 %
0/100 %	41 W	91.4 %	1.8 %
50/25 %	33 W	88.5 %	1.4 %
50/50 %	36 W	93.1 %	1.6 %
50/100 %	45 W	95.2 %	2.0 %
90/50 %	39 W	95.7 %	1.7 %
90/100 %	51 W	96.9 %	2.2 %

Temperature Rating	Maximum 40 °C Minimum -15 °C
--------------------	---------------------------------

Additional Information

Product Main Type	ACH580-01
Product Name	Frequency converter

Classifications

ETIM 8	EC001857 - Frequency converter =< 1 kV
ETIM 9	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

Environmental

SCIP	85773b93-5c45-45c8-a538-ebdaaf96ece Finland (FI)
------	--

---

## Categories

---

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-01 - Wall-mounted drive for HVAC

