

PRODUCT-DETAILS

ACS880-04F-634A-5

LV AC industrial flange-mounted single drive module, IEC: Pn 450 kW, 634 A, 500 V, UL: Pld 500 Hp, 623 A, 480 V (ACS880-04F-634A-5)



General Information

Global Commercial Alias	ACS880-04F-634A-5
Product ID	3AXD50000046018
ABB Type Designation	ACS880-04F-634A-5
EAN	6438177500469
Catalog Description	LV AC industrial flange-mounted single drive module, IEC: Pn 450 kW, 634 A, 500 V, UL: Pld 500 Hp, 623 A, 480 V (ACS880-04F-634A-5)
Long Description	Flange mounting (push through mounting) version of ACS880-04

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044086
Invoice Description	ACS880-04F-634A-5 PN: 450 kW, IN: 634 A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Container Information	
Gross Volume	413.562 dm ³

Dimensions	
Product Net Weight	219 kg 482.813 lb
Product Net Depth / Length	405 mm
Product Net Height	1647 mm
Product Net Width	620 mm
Package Level 1 Depth / Length	2044 mm
Package Level 1 Height	700 mm
Package Level 1 Width	815 mm

Technical	
Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Altitude	4000 m
Sound dB (A)	75 dB(A)
Multiple Battery Information	Lithium Coin, CR2032, 220 mAh, 3 V, 2 pcs, 6 g
Frequency (f)	47.5 ... 63 Hz
Frame Size	R11
Input Voltage (U _{in})	380 ... 500 V
Mounting Type	Module
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIsafe PROFIBUS PROFINET IO
Number of Hardware Interfaces	Industrial Ethernet 0 Other 4 Parallel 0 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	Control unit PC connection
Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	6 / 2
Output Current, Heavy-Duty Use (I _{HD})	477 A
Output Current, Light-Overload Use (I _{LD})	623 A
Output Current, Normal	634 A

Use (I_n)	
Output Power, Heavy-	315 kW
Duty Use (P_{HD})	
Output Power, Light-	450 kW
Overload Use (P_{LD})	
Output Power, Normal	450 kW
Use (P_n)	
Apparent Power Output	549 kV·A
Efficiency Level	IE2
Standby Loss	476 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	2008 W	0.4 %	93.6 %
0 / 50 %	2750 W	0.5 %	95.4 %
0 / 100 %	4686 W	0.9 %	96.1 %
50 / 25 %	2142 W	0.4 %	96.6 %
50 / 50 %	2997 W	0.5 %	97.6 %
50 / 100 %	5381 W	1.0 %	97.8 %
90 / 50 %	3424 W	0.6 %	98.4 %
90 / 100 %	6579 W	1.2 %	98.5 %

Temperature Rating	Maximum 40 °C
--------------------	---------------

Additional Information	
Product Main Type	ACS880-04F
Product Name	Frequency converter

Classifications	
ETIM 8	EC001857 - Frequency converter =< 1 kV
ETIM 9	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

Environmental	
SCIP	d1352974-9712-4b98-83e4-1a826698600c Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 drive modules → ACS880-04F - Single drive module (flange-mounted)

