

PRODUCT-DETAILS

ACQ580-01-09A5-4

LV AC wall-mounted drive for water and wastewater, IEC: Pn 4.0 kW, 9.4 A, 400 V (ACQ580-01-09A5-4)



General Information

Global Commercial Alias	ACQ580-01-09A5-4
Product ID	3AXD50000039020
ABB Type Designation	ACQ580-01-09A5-4
EAN	6438177459705
Catalog Description	LV AC wall-mounted drive for water and wastewater, IEC: Pn 4.0 kW, 9.4 A, 400 V (ACQ580-01-09A5-4)

Long Description	<p>The ACQ580-01 drives deliver innovative pump features for the water and wastewater industry, securing energy efficient flow of water and wastewater in your pumping solutions. This robust and compact wall-mounted drive has built-in pump application functionality such as sensorless flow calculation, multipump control, level control, soft pipe fill, dry run protection, quick ramps and a solution for keeping the impeller of the pump clean.</p> <p>Usability is further enhanced with the intuitive Hand-Off-Auto control panel, the PC tool Drive composer and an optional Bluetooth® control panel. The built-in energy calculator visualizes the energy savings achieved with the use of the drive. The ACQ580-01 variant comes in IP21 enclosure as standard and can be installed on the wall. Also, IP55 and flange mounting units are available.</p>
------------------	---

Ordering

Country of Origin	Romania (RO) Finland (FI) China (CN)
-------------------	--

Customs Tariff Number	85044085
Invoice Description	ACQ580-01-09A5-4 PN: 4.0 kW, IN: 9.4 A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	10.397 dm³
--------------	------------

Dimensions

Product Net Weight	4.60 kg 10.141 lb
Product Net Depth / Length	223 mm 8.78 in
Product Net Height	373 mm 14.69 in
Product Net Width	125 mm 4.92 in
Package Level 1 Depth / Length	225.00 mm 8.86 in
Package Level 1 Height	370.00 mm 14.57 in
Package Level 1 Width	526.00 mm 20.71 in
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Altitude	4000 m 95
Power Factor	0.98
Sound dB (A)	59 dB(A)
Multiple Battery Information	Lithium Coin; CR2032; 220 mAh; 3 V; 1 pc; 3 g
Frequency (f)	47.5 ... 63 Hz
Frame Size	R1
Input Voltage (U _{in})	380 ... 480 V
Mounting Type	Wall-mounted
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Other 2 Parallel 2

	PROFINET 0
	RS-232 0
	RS-422 0
	RS-485 1
	Serial TTY 0
	USB 1
Includes	Control unit PC connection
Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	6 / 3
Output Current, Heavy-Duty Use (I_{HD})	7.2 A
Output Current, Light-Overload Use (I_{LD})	8.9 A
Output Current, Normal Use (I_n)	9.4 A
Output Power, Heavy-Duty Use (P_{HD})	3.0 kW
Output Power, Light-Overload Use (P_{LD})	4.0 kW
Output Power, Normal Use (P_n)	4.0 kW
Apparent Power Output	6.5 kV·A
Efficiency Level	IE2
Standby Loss	14 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Efficiency	Relative Loss
0/25 %	62 W	84.7 %	1.0 %
0/50 %	74 W	90.0 %	1.1 %
0/100 %	105 W	92.1 %	1.6 %
50/25 %	66 W	91.6 %	1.0 %
50/50 %	81 W	94.5 %	1.2 %
50/100 %	118 W	95.6 %	1.8 %
90/50 %	88 W	96.6 %	1.4 %
90/100 %	136 W	97.1 %	2.1 %

Temperature Rating	Maximum 40 °C Minimum -15 °C
--------------------	---------------------------------

Additional Information

Product Main Type	ACQ580-01
Product Name	Frequency converter

Classifications

ETIM 8	EC001857 - Frequency converter =< 1 kV
ETIM 9	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

Environmental	
SCIP	a5c3dd71-8ecd-44d9-98e4-45c53b6836e1 Finland (FI)
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories
Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for water → ACQ580-01 - Wall-mounted drive for water and wastewater

