

PRODUCT-DETAILS

ACS580-07-0880A-4

ACS580-07-0880A-4 PN: 500 kW, IN: 880 A



General Information	
Global Commercial Alias	ACS580-07-0880A-4
Product ID	3AXD50000041433
ABB Type Designation	ACS580-07-0880A-4
Catalog Description	ACS580-07-0880A-4 PN: 500 kW, IN: 880 A
Long Description	The ACS580-07 is plug-in ready to control your compressors, conveyors, pumps, extruders, centrifuges, mixers, fans and many other variable and constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture.
	All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. Versatile and straightforward settings menu and assistants enable fast setup, commissioning, use and maintenance, while rugged and robust design makes it a good fit for various environments. With the ACS580 drives you can easily take full control of your processes to comprehensively manage your plant. The ready-made standalone cabinet-built ACS580-07 variant comes in IP21 as standard. Also, IP42 and IP54 units are available.

Ordering	
Country of Origin	Estonia (EE) Finland (FI)
Customs Tariff Number	85044085
Invoice Description	ACS580-07-0880A-4 PN: 500 kW, IN: 880 A
Made To Order	Yes

Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	1.243 m³
--------------	----------

Dimensions

Product Net Weight	440 kg 970.035 lb
Product Net Depth / Length	698 mm 27.480 in
Product Net Height	2145 mm 84.449 in
Product Net Width	830 mm 32.677 in
Package Level 1 Depth / Length	1100 mm 43.307 in
Package Level 1 Height	2550 mm 100.394 in
Package Level 1 Width	1430 mm 56.299 in

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
	5 to 95%
Sound dB (A)	71 dB(A)
Multiple Battery Information	Lithium Coin, CR2032, 220 mAh, 3 V, 1 pc, 3 g
Frequency (f)	47.5 ... 63 Hz
Frame Size	R11
Input Voltage (U _{in})	380 ... 480 V
Mounting Type	Cabinet-built
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Other 2 Parallel 2 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	Control unit PC connection

Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	6 / 3
Output Current, Heavy-Duty Use (I_{HD})	725 A
Output Current, Light-Overload Use (I_{LD})	865 A
Output Current, Normal Use (I_n)	880 A
Output Power, Heavy-Duty Use (P_{HD})	400 kW
Output Power, Light-Overload Use (P_{LD})	500 kW
Output Power, Normal Use (P_n)	500 kW
Apparent Power Output	610 kV·A
Temperature Rating	Maximum 40 °C Minimum 0 °C
Ecodesign Exemption	Energy efficiency data is not provided for this cabinet-based drive. Cabinet built drives, with already conform modules, are excluded from the scope of the EU ecodesign requirements (Regulation EU/2019/1781, §2.3.e).

Additional Information

Product Main Type	ACS580-07
Product Name	Frequency converter

Classifications

ETIM 8	EC001857 - Frequency converter =< 1 kV
ETIM 9	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

Environmental

SCIP	2361a3f3-2fee-41b4-bbdb-00925564e194 Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → General Purpose Drives → ACS580-07 - Cabinet-built drive

