

PRODUCT-DETAILS

ACH580-07-0585A-4

LV AC cabinet-built drive for HVAC, IEC: Pn 315 kW, 585 A, 400 V, UL: Pld 450 Hp, 573 A, 480 V (ACH580-07-0585A-4)



General Information

Global Commercial Alias	ACH580-07-0585A-4
Product ID	3AXD50000050471
ABB Type Designation	ACH580-07-0585A-4
Catalog Description	LV AC cabinet-built drive for HVAC, IEC: Pn 315 kW, 585 A, 400 V, UL: Pld 450 Hp, 573 A, 480 V (ACH580-07-0585A-4)
Long Description	ACH580 HVAC drive offering has all key features built-in to control fans, pumps and compressors, and more complex equipment like air-handling units and chillers, ensuring smooth, energy-efficient operation of your HVAC systems in normal and mission-critical situations. The built-in features significantly reduce installation time, and the intuitive control panel with an HVAC-specific primary settings menu and help assistants makes startup, commissioning and operation easy. The optional Bluetooth® capability enables the commissioning and monitoring of the drive from a distance. The ready-made standalone cabinet-built ACH580-07 variant comes in IP21 as standard. Also, IP42 and IP54 units are available.

Ordering

Country of Origin	Estonia (EE) Finland (FI)
Customs Tariff Number	85044085
Invoice Description	ACH580-07-0585A-4 PN: 315 kW, IN: 585 A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No

Selling Unit of Measure piece

Container Information

Gross Volume 1.559 m³

Dimensions

Product Net Weight	410 kg 903.896 lb
Product Net Depth / Length	698 mm 27.480 in
Product Net Height	2145 mm 84.449 in
Product Net Width	830 mm 32.677 in
Package Level 1 Depth / Length	1100 mm 43.307 in
Package Level 1 Height	2550 mm
Package Level 1 Width	1430 mm 56.299 in

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
	5 to 95%
Sound dB (A)	72 dB(A)
Multiple Battery Information	Lithium Coin, CR2032, 220 mAh, 3 V, 1 pc, 3 g
Frequency (f)	47.5 ... 63 Hz
Frame Size	R10
Input Voltage (U _{in})	380 ... 480 V
Mounting Type	Cabinet-built
Communication Protocol	BACNET CAN DeviceNet EtherNet/IP LON MODBUS Other Bus Systems PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Other 2 Parallel 2 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	Control unit PC connection
Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	6 / 3
Output Current, Heavy-Duty Use (I _{HD})	429 A

Output Current, Light-Overload Use (I_{LD})	575 A
Output Current, Normal Use (I_n)	585 A
Output Power, Heavy-Duty Use (P_{HD})	250 kW
Output Power, Light-Overload Use (P_{LD})	315 kW
Output Power, Normal Use (P_n)	315 kW
Apparent Power Output	405 kV·A
Temperature Rating	Maximum 40 °C Minimum 0 °C
Ecodesign Exemption	Energy efficiency data is not provided for this cabinet-based drive. Cabinet built drives, with already conform modules, are excluded from the scope of the EU ecodesign requirements (Regulation EU/2019/1781, S2.3.e) .

Additional Information

Product Main Type	ACH580-07
Product Name	Frequency converter

Classifications

ETIM 8	EC001857 - Frequency converter =< 1 kV
ETIM 9	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

Environmental

SCIP	e531a9e8-f7f6-4242-8b63-c885daa80d86 Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-07 - Cabinet-built drive for HVAC

