

PRODUCT-DETAILS

ACS880-37-0101A-5

ACS880-37-0101A-5 PN: 55 kW, IN: 101 A



General Information

Global Commercial Alias	ACS880-37-0101A-5
Product ID	3AXD50000158096
ABB Type Designation	ACS880-37-0101A-5
Catalog Description	ACS880-37-0101A-5 PN: 55 kW, IN: 101 A

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044085
Invoice Description	ACS880-37-0101A-5 PN: 55 kW, IN: 101 A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	320 kg 705 lb
--------------------	------------------

Product Net Depth / Length	673 mm 26.50 in
Product Net Height	2145 mm 84.45 in
Product Net Width	430 mm 16.93 in
Package Level 1 Depth / Length	1100 mm 43.31 in
Package Level 1 Height	2385 mm 93.90 in
Package Level 1 Width	1144 mm 45.04 in

Technical

Number of Phases	3
Degree of Protection	IP22
Enclosure Type NEMA	Type1
Altitude	1000 m 5 ... 95
Power Factor	1
Sound dB (A)	70 dB(A)
Multiple Battery Information	Lithium Coin, CR2032, 2pcs, 3V, 220mAh, 6g
Frequency (f)	48 ... 63 Hz
Frame Size	R8
Input Voltage (U_{in})	380 ... 500 V
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIsafe PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Parallel 0 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	Control unit PC connection
Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	7 / 5
Output Current, Heavy-Duty Use (I_{HD})	77 A
Output Current, Light-Overload Use (I_{LD})	91 A
Output Current, Normal Use (I_N)	101 A
Output Power, Heavy-Duty Use (P_{HD})	45 kW

Output Power, Light-Overload Use (P_{LD})	55 kW
Output Power, Normal Use (P_n)	55 kW
Apparent Power Output	87 kV·A
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current
0/25 %
0/50 %
0/100 %
50/25 %
50/50 %
50/100 %
90/50 %
90/100 %

Temperature Rating	Maximum 40 °C Minimum 0 °C
Ecodesign Exemption	Energy efficiency data is not provided for the drive. The low-harmonic drives are exempt from the EU ecodesign requirements (Regulation EU/2019/1781, §2.3.d).

Additional Information

Product Main Type	ACS880-37
Product Name	Frequency converter

Classifications

ETIM 8	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

Environmental

SCIP	9ECED1FE-316A-4BF4-991E-2606BB5FE13A Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

