

PRODUCT-DETAILS

ACS880-17-1980A-5

ACS880-17-1980A-5



General Information

Global Commercial Alias	ACS880-17-1980A-5
Product ID	3AXD50000145850
ABB Type Designation	ACS880-17-1980A-5
Catalog Description	ACS880-17-1980A-5

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044085
Invoice Description	ACS880-17-1980A-5
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	2930 kg 6460 lb
Product Net Depth / Length	738 mm 29.06 in

Product Net Height	2145 mm 84.45 in
Product Net Width	3230 mm 127.17 in
Package Level 1 Depth / Length	1100 mm 43.31 in
Package Level 1 Height	2376 mm 93.54 in
Package Level 1 Width	3944 mm 155.28 in

Technical

Number of Phases	3
Degree of Protection	IP22
Enclosure Type NEMA	Type1
Altitude	1000 m 5 ... 95
Power Factor	1
Sound dB (A)	78 dB(A)
Multiple Battery Information	Lithium Coin, BR2032, 2pcs, 3V, 200mAh, 3g
Frequency (f)	48 ... 63 Hz
Frame Size	3xR8i+3xR8i
Input Voltage (U_{in})	380 ... 500 V
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIsafe PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Parallel 0 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	Control unit PC connection
Analog Inputs	4
Analog Outputs	4
Number of Digital In/Outputs	14 / 10
Output Current, Heavy- Duty Use (I_{HD})	1481 A
Output Current, Light- Overload Use (I_{LD})	1901 A
Output Current, Normal Use (I_n)	1980 A
Output Power, Heavy- Duty Use (P_{HD})	1000 kW
Output Power, Light- Overload Use (P_{LD})	1300 kW
Output Power, Normal Use (P_n)	1400 kW
Apparent Power Output	1715 kV-A

Complete Drive Module
Efficiency (61800-9-2)

Operating Point Frequency / Current	
	0/25 %
	0/50 %
	0/100 %
	50/25 %
	50/50 %
	50/100 %
	90/50 %
	90/100 %
Temperature Rating	Maximum 40 °C Minimum 0 °C
Ecodesign Exemption	Energy efficiency data is not provided for the drive. The regenerative drives are exempt from the EU ecodesign requirements (Regulation EU/2019/1781, §2.3.c).

Additional Information

Product Main Type	ACS880-17
Product Name	Frequency converter

Classifications

UNSPSC	39122001
--------	----------

Environmental

SCIP	944D8A5E-036D-404E-9036-0D3C1EA703AD Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 single drives → ACS880-17 - Cabinet-built regenerative single drive

