

PRODUCT-DETAILS

ACS380-040C-12A2-2

LV AC machinery drive module, IEC: Pn 3.0 kW, 12.2 A, 230 V, UL: Pld 3.0 Hp, 11.6 A, 230 V (ACS380-040C-12A2-2)



General Information	
Global Commercial Alias	ACS380-040C-12A2-2
Product ID	3AXD50000162130
ABB Type Designation	ACS380-040C-12A2-2
Catalog Description	LV AC machinery drive module, IEC: Pn 3.0 kW, 12.2 A, 230 V, UL: Pld 3.0 Hp, 11.6 A, 230 V (ACS380-040C-12A2-2)
Long Description	The ACS380 machinery drive comes in several variants ensuring seamless integration into machines and connecting perfectly to automation systems. It's a great fit for industries such as food and beverage, material handling and textile. Typical applications include mixers, conveyors, EOT and tower cranes, extruders and textile machinery.
	With the integrated functional safety features, the ACS380 drive can be also part of the machine's safety system via PROFIsafe over PROFINET, ensuring the motor is safely stopped when required. In addition, the drive's software can be easily customized with adaptive programming to match any specific application requirements.

Ordering	
Country of Origin	China (CN) Finland (FI)
Customs Tariff Number	85044086
Invoice Description	ACS380-040C-12A2-2 PN: 3.0 kW, IN: 12.2 A

Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	3.637 dm³
--------------	-----------

Dimensions

Product Net Weight	2.0 kg 4.409 lb
Product Net Depth / Length	176 mm 6.929 in
Product Net Height	223 mm 8.780 in
Product Net Width	95 mm 3.740 in
Package Level 1 Depth / Length	171 mm 6.732 in
Package Level 1 Height	228 mm 8.976 in
Package Level 1 Width	281 mm 11.063 in

Technical

Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Altitude	1000 m
Power Factor	0.98
Sound dB (A)	58.80 dB(A)
Frequency (f)	48 ... 63 Hz
Frame Size	R2
Input Voltage (U _{in})	200 ... 240 V
Mounting Type	Module for cabinet building
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIsafe PROFIBUS PROFINET IO TCP/IP
Number of Hardware	Industrial Ethernet 0

Interfaces

- Other 3
- Parallel 0
- PROFINET 0
- RS-232 0
- RS-422 0
- RS-485 0
- Serial TTY 0
- USB 0

Includes	Control unit PC connection
Analog Inputs	0
Analog Outputs	0
Number of Digital In/Outputs	2 / 1
Output Current, Heavy-Duty Use (I_{HD})	9.8 A
Output Current, Light-Overload Use (I_{LD})	11.6 A
Output Current, Normal Use (I_n)	12.2 A
Output Power, Heavy-Duty Use (P_{HD})	2.2 kW
Output Power, Light-Overload Use (P_{LD})	3.0 kW
Output Power, Normal Use (P_n)	3.0 kW
Apparent Power Output	4.9 kV·A
Efficiency Level	IE2
Standby Loss	15 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Efficiency	Relative Loss
0/25 %	65 W	79.8 %	1.3 %
0/50 %	79 W	86.3 %	1.6 %
0/100 %	114 W	89.0 %	2.3 %
50/25 %	69 W	88.6 %	1.4 %
50/50 %	86 W	92.3 %	1.8 %
50/100 %	129 W	93.7 %	2.6 %
90/50 %	96 W	95.1 %	2.0 %
90/100 %	149 W	95.9 %	3.1 %

Temperature Rating	Maximum 50 °C
--------------------	---------------

Additional Information

Product Main Type	ACS380-040C
Product Name	Base unit

Classifications	
UNSPSC	39122001

Environmental	
SCIP	171cbe90-f958-4bba-b9dd-e62c0f6b4011 Finland (FI)
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories
Drives → Low Voltage AC Drives → Machinery Drives → ACS380 - Machinery Drive

