

PRODUCT-DETAILS

# ACS880-17-1450A-7

## ACS880-17-1450A-7



### General Information

Global Commercial Alias	ACS880-17-1450A-7
Product ID	3AXD50000145942
ABB Type Designation	ACS880-17-1450A-7
Catalog Description	ACS880-17-1450A-7

### Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044085
Invoice Description	ACS880-17-1450A-7
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

### Dimensions

Product Net Weight	2730 kg 6019 lb
--------------------	--------------------

Product Net Depth / Length	698 mm 27.48 in
Product Net Height	2145 mm 84.45 in
Product Net Width	3230 mm 127.17 in
Package Level 1 Depth / Length	1100 mm 43.31 in
Package Level 1 Height	2376 mm 93.54 in
Package Level 1 Width	3944 mm 155.28 in

## Technical

Number of Phases	3
Degree of Protection	IP22
Enclosure Type NEMA	Type1
Altitude	1000 m 5 ... 95
Power Factor	1
Sound dB (A)	78 dB(A)
Multiple Battery Information	Lithium Coin, BR2032, 2pcs, 3V, 200mAh, 3g
Frequency (f)	48 ... 63 Hz
Frame Size	3xR8i+3xR8i
Input Voltage ( $U_{in}$ )	525 ... 690 V
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIsafe PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Parallel 0 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	Control unit PC connection
Analog Inputs	4
Analog Outputs	4
Number of Digital In/Outputs	14 / 10
Output Current, Heavy- Duty Use ( $I_{HD}$ )	1085 A
Output Current, Light- Overload Use ( $I_{LD}$ )	1392 A
Output Current, Normal Use ( $I_n$ )	1450 A
Output Power, Heavy- Duty Use ( $P_{HD}$ )	1000 kW

Output Power, Light-Overload Use ( $P_{LD}$ )	1300 kW
Output Power, Normal Use ( $P_n$ )	1400 kW
Apparent Power Output	1733 kV·A
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current
0/25 %
0/50 %
0/100 %
50/25 %
50/50 %
50/100 %
90/50 %
90/100 %

Temperature Rating	Maximum 40 °C Minimum 0 °C
Ecodesign Exemption	Energy efficiency data is not provided for the drive. The regenerative drives are exempt from the EU ecodesign requirements (Regulation EU/2019/1781, §2.3.c).

Additional Information	
Product Main Type	ACS880-17
Product Name	Frequency converter

Classifications	
UNSPSC	39122001

Environmental	
SCIP	944D8A5E-036D-404E-9036-0D3C1EA703AD Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories	
Drives → Low Voltage AC Drives → Industrial Drives → ACS880 single drives → ACS880-17 - Cabinet-built regenerative single drive	

