

PRODUCT-DETAILS

ACS380-040C-032A-2

LV AC machinery drive module, IEC: Pn 7.5 kW, 32.0 A, 230 V, UL: Pld 10.0 Hp, 30.8 A, 230 V (ACS380-040C-032A-2)



General Information	
Global Commercial Alias	ACS380-040C-032A-2
Product ID	3AXD50000162161
ABB Type Designation	ACS380-040C-032A-2
Catalog Description	LV AC machinery drive module, IEC: Pn 7.5 kW, 32.0 A, 230 V, UL: Pld 10.0 Hp, 30.8 A, 230 V (ACS380-040C-032A-2)
Long Description	The ACS380 machinery drive comes in several variants ensuring seamless integration into machines and connecting perfectly to automation systems. It's a great fit for industries such as food and beverage, material handling and textile. Typical applications include mixers, conveyors, EOT and tower cranes, extruders and textile machinery.
	With the integrated functional safety features, the ACS380 drive can be also part of the machine's safety system via PROFIsafe over PROFINET, ensuring the motor is safely stopped when required. In addition, the drive's software can be easily customized with adaptive programming to match any specific application requirements.

Ordering	
Country of Origin	China (CN) Finland (FI)
Customs Tariff Number	85044086
Invoice Description	ACS380-040C-032A-2 PN: 7.5 kW, IN: 32 A

Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	9.953 dm³
--------------	-----------

Dimensions

Product Net Weight	5.3 kg 11.685 lb
Product Net Depth / Length	176 mm 6.929 in
Product Net Height	240 mm 9.449 in
Product Net Width	260 mm 10.236 in
Package Level 1 Depth / Length	288 mm 11.339 in
Package Level 1 Height	241 mm 9.488 in
Package Level 1 Width	354 mm 13.937 in

Technical

Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Altitude	1000 m
Power Factor	0.98
Sound dB (A)	69.00 dB(A)
Frequency (f)	48 ... 63 Hz
Frame Size	R4
Input Voltage (U _{in})	200 ... 240 V
Mounting Type	Module for cabinet building
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIsafe PROFIBUS PROFINET IO TCP/IP
Number of Hardware	Industrial Ethernet 0

Interfaces

- Other 3
- Parallel 0
- PROFINET 0
- RS-232 0
- RS-422 0
- RS-485 0
- Serial TTY 0
- USB 0

Includes	Control unit PC connection
Analog Inputs	0
Analog Outputs	0
Number of Digital In/Outputs	2 / 1
Output Current, Heavy-Duty Use (I_{HD})	25.0 A
Output Current, Light-Overload Use (I_{LD})	30.8 A
Output Current, Normal Use (I_n)	32.0 A
Output Power, Heavy-Duty Use (P_{HD})	5.5 kW
Output Power, Light-Overload Use (P_{LD})	7.5 kW
Output Power, Normal Use (P_n)	7.5 kW
Apparent Power Output	13 kV·A
Efficiency Level	IE2
Standby Loss	33 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Efficiency	Relative Loss
0/25 %	124 W	84.5 %	1.0 %
0/50 %	159 W	89.1 %	1.2 %
0/100 %	269 W	90.6 %	2.1 %
50/25 %	132 W	91.4 %	1.0 %
50/50 %	175 W	93.9 %	1.4 %
50/100 %	306 W	94.7 %	2.4 %
90/50 %	197 W	96.1 %	1.5 %
90/100 %	350 W	96.5 %	2.7 %

Temperature Rating	Maximum 50 °C
--------------------	---------------

Additional Information

Product Main Type	ACS380-040C
Product Name	Base unit

Classifications	
UNSPSC	39122001

Environmental	
SCIP	cb415b59-4237-4c11-b542-bb9f3de4d187 Finland (FI)
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories	
Drives → Low Voltage AC Drives → Machinery Drives → ACS380 - Machinery Drive	

