

PRODUCT-DETAILS

ACS880-17-3310A-7

ACS880-17-3310A-7



General Information

Global Commercial Alias	ACS880-17-3310A-7
Product ID	3AXD50000145997
ABB Type Designation	ACS880-17-3310A-7
Catalog Description	ACS880-17-3310A-7

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044085
Invoice Description	ACS880-17-3310A-7
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	4980 kg 10979 lb
--------------------	---------------------

Product Net Depth / Length	738 mm 29.06 in
Product Net Height	2145 mm 84.45 in
Product Net Width	5330 mm 209.84 in
Package Level 1 Depth / Length	- mm - in
Package Level 1 Width	- mm - in

Technical

Number of Phases	3
Degree of Protection	IP22
Enclosure Type NEMA	Type1
	5 ... 95
Power Factor	1
Multiple Battery Information	Lithium Coin, BR2032, 2pcs, 3V, 200mAh, 3g
Frequency (f)	48 ... 63 Hz
Frame Size	6xR8i+6xR8i
Input Voltage (U _{in})	525 ... 690 V
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIsafe PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Parallel 0 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	Control unit PC connection
Analog Inputs	4
Analog Outputs	4
Number of Digital In/Outputs	14 / 10
Output Current, Heavy-Duty Use (I _{HD})	2476 A
Output Current, Light-Overload Use (I _{LD})	3178 A
Output Current, Normal Use (I _n)	3310 A
Output Power, Heavy-Duty Use (P _{HD})	2400 kW
Output Power, Light-Overload Use (P _{LD})	3000 kW
Output Power, Normal	3200 kW

Use (P_n)

Apparent Power Output	3956 kV-A
Complete Drive Module	
Efficiency (61800-9-2)	

Operating Point Frequency / Current
0/25 %
0/50 %
0/100 %
50/25 %
50/50 %
50/100 %
90/50 %
90/100 %

Ecodesign Exemption	Energy efficiency data is not provided for the drive. The regenerative drives are exempt from the EU ecodesign requirements (Regulation EU/2019/1781, §2.3.c).
---------------------	--

Additional Information

Product Main Type	ACS880-17
Product Name	Frequency converter

Classifications

UNSPSC	39122001
--------	----------

Environmental

SCIP	944D8A5E-036D-404E-9036-0D3C1EA703AD Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 single drives → ACS880-17 - Cabinet-built regenerative single drive

