



## PRODUCT-DETAILS

# ACQ580-01-04A6-2+P918

## LV AC wall-mounted drive for water and wastewater, 208 ... 240 V (ACQ580-01-04A6-2+P918)

### General Information

Global Commercial Alias	ACQ580-01-04A6-2+P918
Product ID	3AXD50000268306
ABB Type Designation	ACQ580-01-04A6-2+P918
EAN	6438177537359
Catalog Description	LV AC wall-mounted drive for water and wastewater, 208 ... 240 V (ACQ580-01-04A6-2+P918)

Long Description	The ACQ580-01 drives deliver innovative pump features for the water and wastewater industry, securing energy efficient flow of water and wastewater in your pumping solutions. This robust and compact wall-mounted drive has built-in pump application functionality such as sensorless flow calculation, multipump control, level control, soft pipe fill, dry run protection, quick ramps and a solution for keeping the impeller of the pump clean. Usability is further enhanced with the intuitive Hand-Off-Auto control panel, the PC tool Drive composer and an optional Bluetooth® control panel. The built-in energy calculator visualizes the energy savings achieved with the use of the drive. The ACQ580-01 variant comes in IP21 enclosure as standard and can be installed on the wall. Also, IP55 and flange mounting units are available.
------------------	---

### Ordering

Country of Origin	Finland (FI) China (CN)
Customs Tariff Number	85044080
Invoice Description	ACQ580-01-04A6-2, 230VAC, Pn 0.75HP, I2LD 3.5A, N1/IP21
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

### Dimensions

Product Net Weight	10.1 lb
Product Net Depth / Length	8.78 in
Product Net Height	14.69 in
Product Net Width	4.82 in
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	50/60 Hz
Frame Size	R1
Input Voltage (U <sub>in</sub> )	208 ... 240 V
Mounting Type	Wall-mounting
Apparent Power Output	1.8 kV·A
Efficiency Level	IE2
Standby Loss	13 W
Complete Drive Module	
Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	30 W	1.6 %	76.4 %
0 / 50 %	33 W	1.8 %	85.1 %
0 / 100 %	40 W	2.2 %	89.8 %
50 / 25 %	31 W	1.7 %	86.7 %
50 / 50 %	35 W	1.9 %	91.8 %
50 / 100 %	43 W	2.4 %	94.4 %
90 / 50 %	38 W	2.1 %	94.9 %
90 / 100 %	50 W	2.7 %	96.3 %

Temperature Rating	Maximum 40 °C
--------------------	---------------

Additional Information

Product Name	AC Drive
--------------	----------

Classifications

UNSPSC	39122001
--------	----------

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

---

## Categories

---

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for water → ACQ580-01 - Wall-mounted drive for water and wastewater