



PRODUCT-DETAILS

ACQ580-01-059A-2+B056+P918

LV AC wall-mounted drive for water and wastewater, 208 ... 240 V (ACQ580-01-059A-2+B056+P918)

General Information

Global Commercial Alias	ACQ580-01-059A-2+B056+P918
Product ID	3AXD50000268726
ABB Type Designation	ACQ580-01-059A-2+B056+P918
EAN	6438177538073
Catalog Description	LV AC wall-mounted drive for water and wastewater, 208 ... 240 V (ACQ580-01-059A-2+B056+P918)

Long Description	The ACQ580-01 drives deliver innovative pump features for the water and wastewater industry, securing energy efficient flow of water and wastewater in your pumping solutions. This robust and compact wall-mounted drive has built-in pump application functionality such as sensorless flow calculation, multipump control, level control, soft pipe fill, dry run protection, quick ramps and a solution for keeping the impeller of the pump clean. Usability is further enhanced with the intuitive Hand-Off-Auto control panel, the PC tool Drive composer and an optional Bluetooth® control panel. The built-in energy calculator visualizes the energy savings achieved with the use of the drive. The ACQ580-01 variant comes in IP21 enclosure as standard and can be installed on the wall. Also, IP55 and flange mounting units are available.
------------------	---

Ordering

Country of Origin	Finland (FI) China (CN)
Customs Tariff Number	85044080
Invoice Description	ACQ580-01-059A-2+B056, PLD 20 HP, I2LD 59 A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	29 lb
Product Net Depth / Length	9.32 in
Product Net Height	19.29 in
Product Net Width	8.11 in
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP55
Enclosure Type NEMA	Type12
Frequency (f)	50/60 Hz
Frame Size	R3
Input Voltage (U _{in})	208 ... 240 V
Mounting Type	Wall-mounting
Output Current, Light-Overload Use (I _{LD})	59.4 A
Output Power, Light-Overload Use (P _{LD})	20 Hp
Apparent Power Output	24 kV·A
Efficiency Level	IE2
Standby Loss	15 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	211 W	0.9 %	85.6 %
0 / 50 %	273 W	1.2 %	89.9 %
0 / 100 %	480 W	2.0 %	91.0 %
50 / 25 %	229 W	1.0 %	91.9 %
50 / 50 %	307 W	1.3 %	94.3 %
50 / 100 %	577 W	2.4 %	94.6 %
90 / 50 %	360 W	1.5 %	96.2 %
90 / 100 %	767 W	3.2 %	95.9 %

Temperature Rating	Maximum 40 °C
--------------------	---------------

Additional Information

Product Name	AC Drive
--------------	----------

Classifications

UNSPSC	39122001
--------	----------

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
---------------	---

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for water → ACQ580-01 - Wall-mounted drive for water and wastewater