

PRODUCT-DETAILS

# ACS580-01-115A-2

LV AC general purpose wall-mounted drive,  
IEC: Pn 30 kW, 115 A, 230 V (ACS580-01-115A-2)



## General Information

Global Commercial Alias	ACS580-01-115A-2
Product ID	3AXD50000417445
ABB Type Designation	ACS580-01-115A-2
EAN	6438177591269
Catalog Description	LV AC general purpose wall-mounted drive, IEC: Pn 30 kW, 115 A, 230 V (ACS580-01-115A-2)

Long Description	<p>The ACS580-01 is plug-in ready to control your compressors, conveyors, pumps, extruders, centrifuges, mixers, fans and many other variable and constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture.</p> <p>All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. Versatile and straightforward settings menu and assistants enable fast setup, commissioning, use and maintenance, while rugged and robust design makes it a good fit for various environments. With the ACS580 drives you can easily take full control of your processes to comprehensively manage your plant. The wall-mounted ACS580-01 comes in IP21 enclosure as standard. Also, IP55 and flange mounting units are available.</p>
------------------	--

## Ordering

Country of Origin	United States (US) Finland (FI)
Customs Tariff Number	85044085
Invoice Description	ACS580-01-115A-2 PN: 30 kW, IN: 115 A

Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	43.836 dm³
--------------	------------

Dimensions

Product Net Weight	28.3 kg 62.391 lb
Product Net Depth / Length	295.00 mm 11.61 in
Product Net Height	732.00 mm 28.82 in
Product Net Width	203.00 mm 7.99 in
Package Level 1 Depth / Length	835.00 mm
Package Level 1 Height	521.00 mm
Package Level 1 Width	295.00 mm

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Altitude	1000 m 95
Sound dB (A)	63 dB(A)
Multiple Battery Information	Lithium Coin, CR2032, 220 mAh, 3 V, 1 pc, 3 g
Frequency (f)	47.5 ... 63 Hz
Frame Size	R5
Input Voltage (U <sub>in</sub> )	200 ... 240 V
Mounting Type	Wall-mounted
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Other 2 Parallel 2 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	Control unit

	PC connection
Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	6 / 3
Output Current, Heavy-Duty Use ( $I_{HD}$ )	88 A
Output Current, Light-Overload Use ( $I_{LD}$ )	114 A
Output Current, Normal Use ( $I_n$ )	115 A
Output Power, Heavy-Duty Use ( $P_{HD}$ )	22.0 kW
Output Power, Light-Overload Use ( $P_{LD}$ )	30 kW
Output Power, Normal Use ( $P_n$ )	30 kW
Apparent Power Output	46 kV·A
Efficiency Level	IE2
Standby Loss	19 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Efficiency	Relative Loss
0/25 %	321 W	88.3 %	0.7 %
0/50 %	437 W	91.5 %	1.0 %
0/100 %	814 W	92.0 %	1.8 %
50/25 %	352 W	93.5 %	0.8 %
50/50 %	496 W	95.2 %	1.1 %
50/100 %	977 W	95.2 %	2.1 %
90/50 %	590 W	96.8 %	1.3 %
90/100 %	1285 W	96.5 %	2.8 %

Temperature Rating	Maximum 40 °C Minimum -15 °C
--------------------	---------------------------------

Additional Information

Product Main Type	ACS580-01
Product Name	Frequency converter

Classifications

ETIM 8	EC001857 - Frequency converter =< 1 kV
ETIM 9	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

Environmental

SCIP	78feb6f4-2343-45e6-a509-fef3119deda6 Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

---

## Categories

---

Drives → Low Voltage AC Drives → General Purpose Drives → ACS580-01 - Wall-mounted drive

