



PRODUCT-DETAILS

ACQ580-01-10A6-2+B056+P918

LV AC wall-mounted drive for water and wastewater, 208 ... 240 V (ACQ580-01-10A6-2+B056+P918)

General Information

Global Commercial Alias	ACQ580-01-10A6-2+B056+P918
Product ID	3AXD50000268771
ABB Type Designation	ACQ580-01-10A6-2+B056+P918
EAN	6438177538127
Catalog Description	LV AC wall-mounted drive for water and wastewater, 208 ... 240 V (ACQ580-01-10A6-2+B056+P918)

Long Description	The ACQ580-01 drives deliver innovative pump features for the water and wastewater industry, securing energy efficient flow of water and wastewater in your pumping solutions. This robust and compact wall-mounted drive has built-in pump application functionality such as sensorless flow calculation, multipump control, level control, soft pipe fill, dry run protection, quick ramps and a solution for keeping the impeller of the pump clean. Usability is further enhanced with the intuitive Hand-Off-Auto control panel, the PC tool Drive composer and an optional Bluetooth® control panel. The built-in energy calculator visualizes the energy savings achieved with the use of the drive. The ACQ580-01 variant comes in IP21 enclosure as standard and can be installed on the wall. Also, IP55 and flange mounting units are available.
------------------	---

Ordering

Country of Origin	Finland (FI) China (CN)
Customs Tariff Number	85044080
Invoice Description	ACQ580-01-10A6-2+B056, PLD 3 HP, I2LD 10.6 A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	11 lb
Product Net Depth / Length	9.17 in
Product Net Height	15.86 in
Product Net Width	5.06 in
Package Level 1 Units	1 carton

Technical	
Number of Phases	3
Degree of Protection	IP55
Enclosure Type NEMA	Type12
Frequency (f)	50/60 Hz
Frame Size	R1
Input Voltage (U_{in})	208 ... 240 V
Mounting Type	Wall-mounting
Output Current, Light- Overload Use (I_{LD})	10.6 A
Output Power, Light- Overload Use (P_{LD})	3 Hp
Apparent Power Output	4.2 kV·A
Efficiency Level	IE2
Standby Loss	13 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	50 W	1.2 %	81.6 %
0 / 50 %	60 W	1.4 %	87.9 %
0 / 100 %	82 W	2.0 %	90.7 %
50 / 25 %	53 W	1.3 %	89.8 %
50 / 50 %	65 W	1.5 %	93.3 %
50 / 100 %	95 W	2.3 %	94.6 %
90 / 50 %	74 W	1.7 %	95.6 %
90 / 100 %	121 W	2.9 %	96.1 %

Temperature Rating	Maximum 40 °C
--------------------	---------------

Additional Information	
Product Name	AC Drive

Classifications	
UNSPSC	39122001

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for water → ACQ580-01 - Wall-mounted drive for water and wastewater