

## PRODUCT-DETAILS

# ACS580-01-276A-2+B056

LV AC general purpose wall-mounted drive, IEC:  
Pn 75 kW, 276 A, 230 V (ACS580-01-276A-  
2+B056)



### General Information

Global Commercial Alias	ACS580-01-276A-2+B056
Product ID	3AXD50000417636
ABB Type Designation	ACS580-01-276A-2+B056
EAN	6438177591450
Catalog Description	LV AC general purpose wall-mounted drive, IEC: Pn 75 kW, 276 A, 230 V (ACS580-01-276A-2+B056)
Long Description	<p>The ACS580-01 is plug-in ready to control your compressors, conveyors, pumps, extruders, centrifuges, mixers, fans and many other variable and constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture.</p> <p>All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. Versatile and straightforward settings menu and assistants enable fast setup, commissioning, use and maintenance, while rugged and robust design makes it a good fit for various environments. With the ACS580 drives you can easily take full control of your processes to comprehensively manage your plant. The wall-mounted ACS580-01 comes in IP21 enclosure as standard. Also, IP55 and flange mounting units are available.</p>

### Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	850440
Invoice Description	ACS580-01-276A-2+B056 PN: 75 kW, IN: 276 A
Made To Order	Yes
Minimum Order Quantity	1 piece

Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	130.854 dm³
--------------	-------------

Dimensions

Product Net Weight	77 kg 169.756 lb
Product Net Depth / Length	452 mm 17.795 in
Product Net Height	965.00 mm 37.992 in
Product Net Width	300 mm 11.811 in
Package Level 1 Depth / Length	1145.00 mm 45.079 in
Package Level 1 Height	630.00 mm 24.803 in
Package Level 1 Width	485.00 mm 19.094 in

Technical

Number of Phases	3
Degree of Protection	IP55
Enclosure Type NEMA	Type12
	95
Multiple Battery Information	Lithium Coin, CR2032, 220 mAh, 3 V, 1 pc, 3 g
Frequency (f)	47.5 ... 63 Hz
Frame Size	R8
Input Voltage (U <sub>in</sub> )	200 ... 240 V
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Other 2 Parallel 2 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	With control unit Without optical interface With PC connection
Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	6 / 3
Output Current, Heavy-Duty Use (I <sub>HD</sub> )	211 A

Output Current, Light-Overload Use ( $I_{LD}$ )	273 A
Output Current, Normal Use ( $I_n$ )	276 A
Output Power, Heavy-Duty Use ( $P_{HD}$ )	55 kW
Output Power, Light-Overload Use ( $P_{LD}$ )	75 kW
Output Power, Normal Use ( $P_n$ )	75 kW
Apparent Power Output	110 kV·A
Efficiency Level	IE2
Standby Loss	26 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Efficiency	Relative Loss
0/25 %	789 W	88.4 %	0.7 %
0/50 %	1128 W	91.1 %	1.0 %
0/100 %	2160 W	91.3 %	2.0 %
50/25 %	868 W	93.5 %	0.8 %
50/50 %	1283 W	94.9 %	1.2 %
50/100 %	2594 W	94.8 %	2.4 %
90/50 %	1586 W	96.4 %	1.4 %
90/100 %	3571 W	96.0 %	3.2 %

Temperature Rating	Maximum 40 °C Minimum -15 °C
--------------------	---------------------------------

Additional Information

Product Main Type	ACS580-01
Product Name	Frequency converter

Classifications

ETIM 8	EC001857 - Frequency converter =< 1 kV
ETIM 9	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

Environmental

SCIP	9bc1c3a5-044b-4b84-a7d2-7d41a29f4caa Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

---

## Categories

---

Drives → Low Voltage AC Drives → General Purpose Drives → ACS580-01 - Wall-mounted drive

