

PRODUCT-DETAILS

ACS580-01-07A6-2

LV AC general purpose wall-mounted drive, IEC: Pn 1.5 kW, 7.6 A, 230 V (ACS580-01-07A6-2)



General Information	
Global Commercial Alias	ACS580-01-07A6-2
Product ID	3AXD50000417360
ABB Type Designation	ACS580-01-07A6-2
EAN	6438177591085
Catalog Description	LV AC general purpose wall-mounted drive, IEC: Pn 1.5 kW, 7.6 A, 230 V (ACS580-01-07A6-2)
Long Description	<p>The ACS580-01 is plug-in ready to control your compressors, conveyors, pumps, extruders, centrifuges, mixers, fans and many other variable and constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture.</p> <p>All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. Versatile and straightforward settings menu and assistants enable fast setup, commissioning, use and maintenance, while rugged and robust design makes it a good fit for various environments. With the ACS580 drives you can easily take full control of your processes to comprehensively manage your plant. The wall-mounted ACS580-01 comes in IP21 enclosure as standard. Also, IP55 and flange mounting units are available.</p>

Ordering	
Country of Origin	China (CN) Finland (FI) United States (US)
Customs Tariff Number	85044085

Invoice Description	ACS580-01-07A6-2 PN: 1.5 kW, IN: 7.6 A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	10.397 dm³
--------------	------------

Dimensions

Product Net Weight	4.6 kg 10.141 lb
Product Net Depth / Length	223.00 mm 8.78 in
Product Net Height	373.00 mm 14.69 in
Product Net Width	125.00 mm 4.92 in
Package Level 1 Depth / Length	225.00 mm
Package Level 1 Height	370.00 mm
Package Level 1 Width	526.00 mm

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Altitude	1000 m 95
Sound dB (A)	59 dB(A)
Multiple Battery Information	Lithium Coin, CR2032, 220 mAh, 3 V, 1 pc, 3 g
Frequency (f)	47.5 ... 63 Hz
Frame Size	R1
Input Voltage (U _{in})	200 ... 240 V
Mounting Type	Wall-mounted
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Other 2 Parallel 2 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1

Includes	Control unit PC connection
Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	6 / 3
Output Current, Heavy-Duty Use (I_{HD})	6.6 A
Output Current, Light-Overload Use (I_{LD})	7.5 A
Output Current, Normal Use (I_n)	7.6 A
Output Power, Heavy-Duty Use (P_{HD})	1.1 kW
Output Power, Light-Overload Use (P_{LD})	1.5 kW
Output Power, Normal Use (P_n)	1.5 kW
Apparent Power Output	3.0 kV·A
Efficiency Level	IE2
Standby Loss	13 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Efficiency	Relative Loss
0/25 %	40 W	80.0 %	1.3 %
0/50 %	46 W	87.1 %	1.5 %
0/100 %	60 W	90.6 %	2.0 %
50/25 %	42 W	88.8 %	1.4 %
50/50 %	49 W	92.9 %	1.6 %
50/100 %	67 W	94.7 %	2.2 %
90/50 %	55 W	95.5 %	1.8 %
90/100 %	82 W	96.3 %	2.7 %

Temperature Rating	Maximum 40 °C Minimum -15 °C
--------------------	---------------------------------

Additional Information

Product Main Type	ACS580-01
Product Name	Frequency converter

Classifications

ETIM 8	EC001857 - Frequency converter =< 1 kV
ETIM 9	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

Environmental

SCIP	8105d671-49fa-4c1c-836d-baf56982886a Finland (FI)
------	---

Categories

Drives → Low Voltage AC Drives → General Purpose Drives → ACS580-01 - Wall-mounted drive

