

PRODUCT-DETAILS

# ACQ580-01-04A7-2

## LV AC wall-mounted drive for water and wastewater, IEC: Pn 0.75 kW, 4.7 A, 230 V (ACQ580-01-04A7-2)



General Information	
Global Commercial Alias	ACQ580-01-04A7-2
Product ID	3AXD50000417940
ABB Type Designation	ACQ580-01-04A7-2
EAN	6438177591764
Catalog Description	LV AC wall-mounted drive for water and wastewater, IEC: Pn 0.75 kW, 4.7 A, 230 V (ACQ580-01-04A7-2)
Long Description	The ACQ580-01 drives deliver innovative pump features for the water and wastewater industry, securing energy efficient flow of water and wastewater in your pumping solutions. This robust and compact wall-mounted drive has built-in pump application functionality such as sensorless flow calculation, multipump control, level control, soft pipe fill, dry run protection, quick ramps and a solution for keeping the impeller of the pump clean.
	Usability is further enhanced with the intuitive Hand-Off-Auto control panel, the PC tool Drive composer and an optional Bluetooth® control panel. The built-in energy calculator visualizes the energy savings achieved with the use of the drive. The ACQ580-01 variant comes in IP21 enclosure as standard and can be installed on the wall. Also, IP55 and flange mounting units are available.

Ordering	
Country of Origin	China (CN) Finland (FI) United States (US)

Customs Tariff Number	85044085
Invoice Description	ACQ580-01-04A7-2 PN: 0.75 kW, IN: 4.7 A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	10.397 dm³
--------------	------------

Dimensions

Product Net Weight	4.60 kg 10.141 lb
Product Net Depth / Length	223 mm 8.78 in
Product Net Height	373 mm 14.69 in
Product Net Width	125 mm 4.92 in
Package Level 1 Depth / Length	225.00 mm 8.86 in
Package Level 1 Height	370.00 mm 14.57 in
Package Level 1 Width	526.00 mm 20.71 in

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Altitude	4000 m 95
Power Factor	0.98
Sound dB (A)	59 dB(A)
Multiple Battery Information	Lithium Coin; CR2032; 220 mAh; 3 V; 1 pc; 3 g
Frequency (f)	47.5 ... 63 Hz
Frame Size	R1
Input Voltage (U <sub>in</sub> )	200 ... 240 V
Mounting Type	Wall-mounted
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Other 2 Parallel 2 PROFINET 0

	RS-232 0
	RS-422 0
	RS-485 1
	Serial TTY 0
	USB 1
Includes	Control unit PC connection
Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	6 / 3
Output Current, Heavy- Duty Use ( $I_{HD}$ )	3.5 A
Output Current, Light- Overload Use ( $I_{LD}$ )	4.6 A
Output Current, Normal Use ( $I_n$ )	4.7 A
Output Power, Heavy- Duty Use ( $P_{HD}$ )	0.55 kW
Output Power, Light- Overload Use ( $P_{LD}$ )	0.75 kW
Output Power, Normal Use ( $P_n$ )	0.75 kW
Apparent Power Output	1.9 kV-A
Efficiency Level	IE2
Standby Loss	13 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Efficiency	Relative Loss
0/25 %	32 W	75.6 %	1.7 %
0/50 %	35 W	84.6 %	1.9 %
0/100 %	42 W	89.4 %	2.2 %
50/25 %	33 W	86.2 %	1.8 %
50/50 %	37 W	91.5 %	2.0 %
50/100 %	46 W	94.2 %	2.5 %
90/50 %	40 W	94.7 %	2.1 %
90/100 %	53 W	96.2 %	2.8 %

Temperature Rating	Maximum 40 °C Minimum -15 °C
--------------------	---------------------------------

Additional Information	
Product Main Type	ACQ580-01
Product Name	Frequency converter

Classifications	
ETIM 8	EC001857 - Frequency converter =< 1 kV
ETIM 9	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

---

**Environmental**

SCIP	8105d671-49fa-4c1c-836d-baf56982886a Finland (FI)
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

---

---

**Categories**

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for water → ACQ580-01 - Wall-mounted drive for water and wastewater

