

PRODUCT-DETAILS

ACS180-04S-02A4-1

LV AC machinery drive module, IEC: Pn 0.37 kW, 2.4 A (ACS180-04S-02A4-1)



General Information	
Global Commercial Alias	ACS180-04S-02A4-1
Product ID	3AXD50000662500
ABB Type Designation	ACS180-04S-02A4-1
Catalog Description	LV AC machinery drive module, IEC: Pn 0.37 kW, 2.4 A (ACS180-04S-02A4-1)
Long Description	The ACS180 is a compact, robust, and adaptable variable speed drive (VSD) for applications such as pumps, fans, compressors, conveyors, winders and mixers. This easy-to-use compact VSD offers excellent performance and quality at superior value with all essential machinery application features embedded. And as a member of ABB's all-compatible drives portfolio, it shares the same architecture and user interfaces for ease of use.

Ordering	
Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS180-04S-02A4-1 PN: 0.37kW, IN: 2.4A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece

Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	0.92 kg
Product Net Depth / Length	143 mm
Product Net Height	209 mm
Product Net Width	70 mm
Package Level 1 Depth / Length	225 mm
Package Level 1 Height	115 mm
Package Level 1 Width	220 mm
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	R0
Input Voltage (U_{in})	200 ... 240 V
Mounting Type	Module_NO UNIT\$
Output Current, Heavy-Duty Use (I_{HD})	1.8 A
Output Current, Light-Overload Use (I_{LD})	2.3 A
Output Current, Normal Use (I_n)	2.4 A
Output Power, Heavy-Duty Use (P_{HD})	0.25 kW
Output Power, Light-Overload Use (P_{LD})	0.37 kW
Output Power, Normal Use (P_n)	0.37 kW
Efficiency Level	IE2

Additional Information

Product Name	FREQUENCY CONVERTER
--------------	---------------------

Classifications	
UNSPSC	39122001

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories	
Drives → Low Voltage AC Drives → Machinery Drives → ACS180 - Machinery Drive	

