

PRODUCT-DETAILS

ACS180-04S-03A3-4

LV AC machinery drive module, IEC: Pn 1.1 kW, 3.3 A (ACS180-04S-03A3-4)



General Information	
Global Commercial Alias	ACS180-04S-03A3-4
Product ID	3AXD50000662586
ABB Type Designation	ACS180-04S-03A3-4
Catalog Description	LV AC machinery drive module, IEC: Pn 1.1 kW, 3.3 A (ACS180-04S-03A3-4)
Long Description	The ACS180 is a compact, robust, and adaptable variable speed drive (VSD) for applications such as pumps, fans, compressors, conveyors, winders and mixers. This easy-to-use compact VSD offers excellent performance and quality at superior value with all essential machinery application features embedded. And as a member of ABB's all-compatible drives portfolio, it shares the same architecture and user interfaces for ease of use.

Ordering	
Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS180-04S-03A3-4 PN: 1.1kW, IN: 3.3A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	0.92 kg
Product Net Depth / Length	143 mm
Product Net Height	209 mm
Product Net Width	70 mm
Package Level 1 Depth / Length	225 mm
Package Level 1 Height	115 mm
Package Level 1 Width	220 mm
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	R0
Input Voltage (U_{in})	380 ... 480 V
Mounting Type	Module_NO UNIT\$
Output Current, Heavy-Duty Use (I_{HD})	2.4 A
Output Current, Light-Overload Use (I_{LD})	3.1 A
Output Current, Normal Use (I_n)	3.3 A
Output Power, Heavy-Duty Use (P_{HD})	0.75 kW
Output Power, Light-Overload Use (P_{LD})	1.1 kW
Output Power, Normal Use (P_n)	1.1 kW
Apparent Power Output	2.3 kV·A
Efficiency Level	IE2
Standby Loss	7 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	19 W	0.8 %	86.5 %
0 / 50 %	22 W	0.9 %	91.5 %
0 / 100 %	29 W	1.3 %	93.8 %
50 / 25 %	20 W	0.9 %	92.7 %
50 / 50 %	23 W	1.0 %	95.4 %
50 / 100 %	32 W	1.4 %	96.6 %
90 / 50 %	26 W	1.1 %	97.1 %
90 / 100 %	38 W	1.6 %	97.7 %

Temperature RatingMaximum 40 °C

Additional Information

Product NameFREQUENCY CONVERTER

Classifications

UNSPSC39122001

Environmental

WEEE Category5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Machinery Drives → ACS180 - Machinery Drive

