

PRODUCT-DETAILS

ACQ580-PD-04A8-4+B058

LV AC Packaged drive with disconnect and fuses, UL: Pld 3 Hp, 4.8 A, 460 V (ACQ580-PD-04A8-4+B058)



General Information

Global Commercial Alias	ACQ580-PD-04A8-4+B058
Product ID	3AXD50000705504
ABB Type Designation	ACQ580-PD-04A8-4+B058
EAN	6438177645429

Catalog Description	LV AC Packaged drive with disconnect and fuses, UL: Pld 3 Hp, 4.8 A, 460 V (ACQ580-PD-04A8-4+B058)
---------------------	--

Long Description	The ACQ580-PD drives deliver the ACQ580 Product Series features delivering innovative pump features for the water and wastewater industry, securing energy-efficient flow of water and wastewater in your pumping solutions. This robust and compact wall-mounted packaged drive has built-in pump application functionality such as sensorless flow calculation, multi-pump control, level control, soft pipe fill, dry run protection, quick ramps, and a solution for keeping the impeller of the pump clean. Usability is further enhanced with the intuitive Hand-Off-Auto control panel, the PC tool Drive composer, an optional Bluetooth® control panel, and a UL-approved electronic motor overload. The built-in energy calculator visualizes the energy savings achieved with the use of the drive.
------------------	--

Ordering

Country of Origin	United States (US)
Customs Tariff Number	85044080

Invoice Description	ACQ580-PD-04A8-4+B058, PLD 3 HP, I2LD 4.8 A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	77 lb
Product Net Depth / Length	14 in
Product Net Height	33.35 in
Product Net Width	17.7 in

Technical

Number of Phases	3
Enclosure Type NEMA	Type3R
Frequency (f)	50/60 Hz
Frame Size	Undefined
Input Voltage (U _{in})	440 ... 480 V

Additional Information

Product Name	AC Drive
--------------	----------

Classifications

UNSPSC	39121007
--------	----------

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for water → ACQ580-PD - Drive with disconnect US

