

PRODUCT-DETAILS

ACS180-04N-04A0-4

LV AC machinery drive module, IEC: Pn 1.5 kW, 4.0 A, 400 V, UL: Pld 2 Hp, 3.5 A, 460 V (ACS180-04N-04A0-4)



General Information

Global Commercial Alias	ACS180-04N-04A0-4
Product ID	3AXD50000716524
ABB Type Designation	ACS180-04N-04A0-4
EAN	6438177648970
Catalog Description	LV AC machinery drive module, IEC: Pn 1.5 kW, 4.0 A, 400 V, UL: Pld 2 Hp, 3.5 A, 460 V (ACS180-04N-04A0-4)
Long Description	The ACS180 is a compact, robust, and adaptable variable speed drive (VSD) for applications such as pumps, fans, compressors, conveyors, winders and mixers. This easy-to-use compact VSD offers excellent performance and quality at superior value with all essential machinery application features embedded. And as a member of ABB's all-compatible drives portfolio, it shares the same architecture and user interfaces for ease of use.

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044085
Invoice Description	ACS180-04N-04A0-4 PN: 1.5 kW, IN: 4.0 A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece

Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	0.022 hl
--------------	----------

Dimensions

Product Net Weight	1.24 kg 2.734 lb
Product Net Depth / Length	143 mm 5.630 in
Product Net Height	220 mm 8.661 in
Product Net Width	70 mm 2.756 in
Package Level 1 Depth / Length	225 mm 8.858 in
Package Level 1 Height	115 mm 4.528 in
Package Level 1 Width	220 mm 8.661 in

Technical

Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Altitude	1000 m
Power Factor	0.98
Sound dB (A)	50.90 dB(A)
Frequency (f)	47 ... 63 Hz
Frame Size	R1
Input Voltage (U _{in})	380 ... 480 V
Communication Protocol	MODBUS
Number of Hardware Interfaces	Industrial Ethernet 0 Other 1 Parallel 0 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 0
Includes	Control unit PC connection
Analog Inputs	2
Analog Outputs	1
Number of Digital In/Outputs	4 / 2
Output Current, Heavy-Duty Use (I _{HD})	3.3 A
Output Current, Light-	3.8 A

Overload Use (I_{LD})	
Output Current, Normal Use (I_n)	4.0 A
Output Power, Heavy-Duty Use (P_{HD})	1.1 kW
Output Power, Light-Overload Use (P_{LD})	1.5 kW
Output Power, Normal Use (P_n)	1.5 kW
Apparent Power Output	2.8 kV·A
Efficiency Level	IE2
Standby Loss	9 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Efficiency	Relative Loss
0/25 %	23 W	86.7 %	0.8 %
0/50 %	26 W	91.7 %	0.9 %
0/100 %	34 W	93.9 %	1.2 %
50/25 %	24 W	92.9 %	0.8 %
50/50 %	28 W	95.5 %	1.0 %
50/100 %	39 W	96.6 %	1.4 %
90/50 %	31 W	97.2 %	1.1 %
90/100 %	45 W	97.8 %	1.6 %

Temperature Rating	Maximum 40 °C
--------------------	---------------

Additional Information	
Product Main Type	ACS180-04N
Product Name	Frequency converter

Environmental	
SCIP	5d07f008-496e-4abd-8f50-616cb485c791 Finland (FI)
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Machinery Drives → ACS180 - Machinery Drive

