

PRODUCT-DETAILS

ACS530-01-02A7-4+J400

ACS530-01-02A7-4+J400 PN: 0.75kW, IN: 2.6A



General Information	
Global Commercial Alias	ACS530-01-02A7-4+J400
Product ID	3AXD50000751532
ABB Type Designation	ACS530-01-02A7-4+J400
Catalog Description	ACS530-01-02A7-4+J400 PN: 0.75kW, IN: 2.6A
Long Description	<p>The ACS530-01 can control your compressors, conveyors, pumps, centrifuges, fans, and many other variable and simple constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture. All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. The basic control panel enable fast setup, commissioning, use, and maintenance, while a rugged and robust design make it a good fit for various environments.</p> <p>The wall-mounted ACS530-01 comes in an IP20 enclosure as standard.</p>

Ordering	
Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS530-01-02A7-4+J400 PN: 0.75kW, IN: 2.6A
Made To Order	No
Minimum Order Quantity	1 piece

Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	4 kg
Product Net Depth / Length	223 mm
Product Net Height	331 mm
Product Net Width	125 mm
Package Level 1 Depth / Length	525 mm
Package Level 1 Height	425 mm
Package Level 1 Width	225 mm
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	R1
Input Voltage (U_{in})	380 ... 500 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Light-Overload Use (I_{LD})	2.5 A
Output Current, Normal Use (I_n)	2.6 A
Output Power, Light-Overload Use (P_{LD})	0.75 kW
Output Power, Normal Use (P_n)	0.75 kW
Efficiency Level	IE2
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	28 W	1.5 %	77.6 %
0 / 50 %	30 W	1.6 %	86.2 %
0 / 100 %	34 W	1.9 %	90.9 %
50 / 25 %	28 W	1.6 %	87.5 %
50 / 50 %	31 W	1.7 %	92.5 %
50 / 100 %	37 W	2.1 %	95 %
90 / 50 %	33 W	1.8 %	95.4 %
90 / 100 %	42 W	2.3 %	96.8 %

Additional Information

Product NameFrequency Converter

Classifications

UNSPSC39122001

Environmental

WEEE Category5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → General Purpose Drives → ACS530-01 - Wall-mounted drive

