

PRODUCT-DETAILS

ACS180-04N-02A4-1

LV AC machinery drive module, IEC: Pn 0.37 kW, 2.4 A, 230 V, UL: Pld 0.5 Hp, 2.4 A, 230 V (ACS180-04N-02A4-1)



General Information

Global Commercial Alias	ACS180-04N-02A4-1
Product ID	3AXD50000715534
ABB Type Designation	ACS180-04N-02A4-1
EAN	6438177648413
Catalog Description	LV AC machinery drive module, IEC: Pn 0.37 kW, 2.4 A, 230 V, UL: Pld 0.5 Hp, 2.4 A, 230 V (ACS180-04N-02A4-1)
Long Description	The ACS180 is a compact, robust, and adaptable variable speed drive (VSD) for applications such as pumps, fans, compressors, conveyors, winders and mixers. This easy-to-use compact VSD offers excellent performance and quality at superior value with all essential machinery application features embedded. And as a member of ABB's all-compatible drives portfolio, it shares the same architecture and user interfaces for ease of use.

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044085
Invoice Description	ACS180-04N-02A4-1 PN: 0.37 kW, IN: 2.4 A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece

Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	2.092 dm³
--------------	-----------

Dimensions

Product Net Weight	0.92 kg 2.028 lb
Product Net Depth / Length	143 mm 5.630 in
Product Net Height	209 mm 8.228 in
Product Net Width	70 mm 2.756 in
Package Level 1 Depth / Length	225 mm 8.858 in
Package Level 1 Height	115 mm 4.528 in
Package Level 1 Width	220 mm 8.661 in

Technical

Number of Phases	1
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Altitude	1000 m
Power Factor	0.98
Sound dB (A)	- dB(A)
Frequency (f)	47 ... 63 Hz
Frame Size	R0
Input Voltage (U _{in})	200 ... 240 V
Communication Protocol	MODBUS
Number of Hardware Interfaces	Industrial Ethernet 0 Other 1 Parallel 0 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 0
Includes	Control unit PC connection
Analog Inputs	2
Analog Outputs	1
Number of Digital In/Outputs	4 / 2
Output Current, Heavy-Duty Use (I _{HD})	1.8 A
Output Current, Light-	2.4 A

Overload Use (I_{LD})	
Output Current, Normal Use (I_n)	2.4 A
Output Power, Heavy-Duty Use (P_{HD})	0.25 kW
Output Power, Light-Overload Use (P_{LD})	0.37 kW
Output Power, Normal Use (P_n)	0.37 kW
Complete Drive Module Efficiency (61800-9-2)	
Operating Point Frequency / Current	
0/25 %	
0/50 %	
0/100 %	
50/25 %	
50/50 %	
50/100 %	
90/50 %	
90/100 %	

Additional Information

Product Main Type	ACS180-04N
Product Name	Frequency converter

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Categories

Drives → Low Voltage AC Drives → Machinery Drives → ACS180 - Machinery Drive

