

## PRODUCT-DETAILS

# ACS180-04S-055A-2

LV AC machinery drive module, IEC: Pn 11 kW,  
55 A (ACS180-04S-055A-2)



## General Information

Global Commercial Alias	ACS180-04S-055A-2
Product ID	3AXD50000814602
ABB Type Designation	ACS180-04S-055A-2
Catalog Description	LV AC machinery drive module, IEC: Pn 11 kW, 55 A (ACS180-04S-055A-2)
Long Description	The ACS180 is a compact, robust, and adaptable variable speed drive (VSD) for applications such as pumps, fans, compressors, conveyors, winders and mixers. This easy-to-use compact VSD offers excellent performance and quality at superior value with all essential machinery application features embedded. And as a member of ABB's all-compatible drives portfolio, it shares the same architecture and user interfaces for ease of use.

## Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS180-04S-055A-2 PN: 11kW, IN: 55A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

## Container Information

Gross Volume	2.2 dm <sup>3</sup>
--------------	---------------------

## Dimensions

Product Net Weight	5.3 kg
Product Net Depth / Length	178 mm
Product Net Height	206 mm
Product Net Width	260 mm
Package Level 1 Depth / Length	225 mm
Package Level 1 Height	115 mm
Package Level 1 Width	220 mm
Package Level 1 Units	1 carton

## Technical

Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	R4
Input Voltage ( $U_{in}$ )	200 ... 240 V
Mounting Type	Module_NO UNIT\$
Output Current, Heavy-Duty Use ( $I_{HD}$ )	46.2 A
Output Current, Light-Overload Use ( $I_{LD}$ )	50.2 A
Output Current, Normal Use ( $I_n$ )	55 A
Output Power, Heavy-Duty Use ( $P_{HD}$ )	11 kW
Output Power, Light-Overload Use ( $P_{LD}$ )	11 kW
Output Power, Normal Use ( $P_n$ )	11 kW
Efficiency Level	IE2
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	221 W	1.0 %	84.0 %
0 / 50 %	300 W	1.4 %	88.2 %
0 / 100 %	552 W	2.5 %	89.0 %
50 / 25 %	235 W	1.1 %	91.2 %
50 / 50 %	327 W	1.5 %	93.4 %
50 / 100 %	619 W	2.8 %	93.8 %
90 / 50 %	366 W	1.7 %	95.8 %
90 / 100 %	702 W	3.2 %	96.0 %

Additional Information

Product Name	FREQUENCY CONVERTER
--------------	---------------------

Classifications

UNSPSC	39122001
--------	----------

Environmental

SCIP	2fa266a4-ca31-4604-a9f6-9646f8174b5e Finland (FI)
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Machinery Drives → ACS180 - Machinery Drive

