

PRODUCT-DETAILS

ACS180-04N-033A-4

LV AC machinery drive module, IEC: Pn 15 kW, 32 A (ACS180-04N-033A-4)



General Information	
Global Commercial Alias	ACS180-04N-033A-4
Product ID	3AXD50000874163
ABB Type Designation	ACS180-04N-033A-4
Catalog Description	LV AC machinery drive module, IEC: Pn 15 kW, 32 A (ACS180-04N-033A-4)
Long Description	The ACS180 is a compact, robust, and adaptable variable speed drive (VSD) for applications such as pumps, fans, compressors, conveyors, winders and mixers. This easy-to-use compact VSD offers excellent performance and quality at superior value with all essential machinery application features embedded. And as a member of ABB's all-compatible drives portfolio, it shares the same architecture and user interfaces for ease of use.

Ordering	
Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS180-04N-033A-4 PN: 15kW, IN: 32A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece

Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	2.2 dm³
--------------	---------

Dimensions

Product Net Weight	3.3 kg
Product Net Depth / Length	174 mm
Product Net Height	205 mm
Product Net Width	170 mm
Package Level 1 Depth / Length	248 mm
Package Level 1 Height	273 mm
Package Level 1 Width	250 mm
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	R3
Input Voltage (U_{in})	380 ... 480 V
Mounting Type	Module_NO UNIT\$
Output Current, Heavy-Duty Use (I_{HD})	25 A
Output Current, Light-Overload Use (I_{LD})	30.5 A
Output Current, Normal Use (I_n)	32 A
Output Power, Heavy-Duty Use (P_{HD})	11 kW
Output Power, Light-Overload Use (P_{LD})	15 kW
Output Power, Normal Use (P_n)	15 kW
Efficiency Level	IE2
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	125 W	0.6 %	90.3 %
0 / 50 %	180 W	0.8 %	92.6 %
0 / 100 %	339 W	1.5 %	93.0 %
50 / 25 %	134 W	0.6 %	94.8 %
50 / 50 %	192 W	0.9 %	96.1 %
50 / 100 %	414 W	1.9 %	95.8 %
90 / 50 %	206 W	0.9 %	97.6 %
90 / 100 %	551 W	2.5 %	96.9 %

Additional Information

Product Name	FREQUENCY CONVERTER
--------------	---------------------

Classifications

UNSPSC	39122001
--------	----------

Environmental

SCIP	ce087935-c5d0-48c8-89ae-769efc3dfb30 Finland (FI)
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Machinery Drives → ACS180 - Machinery Drive

