



PRODUCT-DETAILS

3BSE094596R1

ABB & Partner Demo License, 800xA 6.0



License

General Information	
Product ID	3BSE094596R1
ABB Type Designation	800xA 6.0
Catalog Description	ABB & Partner Demo License, 800xA 6.0

	800xA license to be used in R&D, permanent demo systems, training, and education systems. System will always be in production mode. License is time limited to 18 month. Use cases: R&D, Permanent Demo centers
	License include: Base system 20,000 tags singular/redundant 20,000 tags multisystem integration subscriber/provider Multi System Provider Connections, 2 Load evaluate go Softpoint server Point of control Snapshot reports
	AC 800M Connect PLC Connect PLC Connect Dial-up AC400 Connect Harmony Connect Melody Connect MOD300 Connect Safeguard Connect DCI Connect Freelance 800F Connect AC100 Connect
	Advant Master Central Backup 800xA OPC Client Connection, 1 OLE-DB Real Time Data-Client Connection, 1 IEC 61850 Connectivity, 1 singular or redundant server Audit Trail Advanced Access Control, Digital Signature, SMS & Email Messaging
	800xA Event Forwarder Calculation Engine Operator Clients, 25 Large Operator Clients, 5 EOW-x2 Operator Workplace, 1 EOW-x3 Operator Workplace, 1 Alarm Management, Alarm History & Reports CAD Viewer, 10 PG2 Symbol Factory Smart Client Workplace, 5
Long Description	Public Address output channels, 2 Public Address languages, 4 cpmPlus Platform ECS Maximo plug-in ECS SAP plug-in
	History Signals, 20 000 Dual History Signals, 20 000 Data Access to Signals, 20 000 Soft Controller, 10 UDP Communication Library, 2 TCP Communication Library, 2 Burner Management Library, for one CPU INFI90 Function Code Library MOD300 CCF Library for AC 800M Substation operation Library AC 800M High Integrity and Process Control, 5
	Engineering Workplaces (incl. Control Builder M, Function Designer & Bulk Data Manager), 19 Application Change Management, (incl SQL Srv), 50,000 Graphics Builder, 9 Script Manager Professional, 19 Reuse Assistant, Library Assistant Asset Monitors, 500 PC, Network, Software Monitoring, 2 000 tags

	Maximo Integration
	SAP integration, SAP / Plant Maintenance Integration
	Advanced Harmony Control System Monitoring
	CLAM Asset monitor, 50
	Generic Heat Exchanger Asset Monitor, 10
	Shell and Tube Heat Exchanger Asset Monitor, 10
	HART Device Integration, 1000
	HART Multiplexer Connect
	Fieldbus Builder HART, 1
	Foundation Fieldbus Device Integration, 1000
	Fieldbus Builder Foundation Fieldbus, 1
	Profibus Device Integration, 1000
	Fieldbus Builder Profibus, 1
	Process Control Device Library, 2500
	PCDeviceLib App Engineering License , 2500
	Process Control Equipment Library With production management, 10
	Process Control Equipment Library Without production management, 10
	ProBase Software License, for 10 CPUs of any type
	Licenses for AC 800M Controllers and Communication interfaces, 50 of each

Additional Information

Medium Description	800xA license to be used in R&D, permanent demo systems, training, and education systems. System will always be in production mode. License is time limited to 18 month. Use cases: R&D, Permanent Demo centers License include: Base system 20,000 tags singular/redundant 20,000 tags multisystem integration subscriber/provider Multi System Provider Connections, 2 Load evaluate go Softpoint server Point of control Snapshot reports AC 800M Connect PLC Connect PLC Connect Dial-up AC400 Connect Harmony Connect Melody Connect MOD300 Connect Safeguard Connect DCI Connect Freelance 800F Connect AC100 Connect Advant Master Central Backup 800xA OPC Client Connection, 1 OLE-DB Real Time Data-Client Connection, 1 IEC 61850 Connectivity, 1 singular or redundant server Audit Trail Advanced Access Control, Digital Signature, SMS & Email Messaging 800xA Event Forwarder Calculation Engine Operator Clients, 25 Large Operator Clients, 5 EOW-x2 Operator Workplace, 1 EOW-x3 Operator Workplace, 1 Alarm Management, Alarm History & Reports CAD Viewer, 10 PG2 Symbol Factory Smart Client Workplace, 5 Public Address output channels, 2 Public Address languages, 4 cpmPlus Platform ECS Maximo plug-in ECS SAP plug-in History Signals, 20 000 Dual History Signals, 20 000 Data Access to Signals, 20 000 Soft Controller, 10 UDP Communication Library, 2 TCP Communication Library, 2 Burner Management Library, for one CPU INFI90 Function Code Library MOD300 CCF Library for AC 800M Substation operation Library AC 800M High Integrity and Process Control, 5 Engineering Workplaces (incl. Control Builder M, Function Designer & Bulk Data Manager), 19 Application Change Management, (incl SQL Srv), 50,000 Graphics Builder, 9 Script Manager Professional, 19 Reuse Assistant, Library Assistant Asset Monitors, 500 PC, Network, Software Monitoring, 2 000 tags Maximo Integration SAP integration, SAP / Plant Maintenance Integration Advanced Harmony Control System Monitoring CLAM Asset monitor, 50 Generic Heat Exchanger Asset Monitor, 10 Shell and Tube Heat Exchanger Asset Monitor, 10 HART Device Integration, 1000 HART Multiplexer Connect Fieldbus Builder HART, 1 Foundation Fieldbus Device Integration, 1000 Fieldbus Builder Foundation Fieldbus, 1 Profibus Device Integration, 1000 Fieldbus Builder Profibus, 1 Process Control Device Library, 2500 PCDeviceLib App Engineering License , 2500 Process Control Equipment Library With production management, 10 Process Control Equipment Library Without production management, 10 ProBase Software License, for 10 CPUs of any type Licenses for AC 800M Controllers and Communication interfaces, 50 of each
Product Type	Licenses

Ordering

Customs Tariff Number

99999999

Dimensions

Product Net Weight

0 kg

Environmental

RoHS Status

No declaration needed

WEEE Category

Product Not in WEEE Scope

Categories

Control System Products → Systems → ABB Ability System 800xA → System 800xA Lic - Base Licenses → ABB & Partner Demo License, 800xA 6.0

Control Systems → 800xA → System → 800xA System → 800xA 6.0 System → Licenses



License