



PRODUCT-DETAILS

3BSC610051R1
MPS022 Power supply



General Information

Product ID	3BSC610051R1
ABB Type Designation	MPS 022
Catalog Description	MPS022 Power supply

Additional Information

ABB Type Designation	MPS 022
Core Credit	0.00
Country of Origin	United States (US) Sweden (SE)
Customs Tariff Number	8504318090
Frame Size	Spare_Parts
Gross Weight	3 kg
Invoice Description	MPS022 Power supply
Made To Order	No
Medium Description	Power supply
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Package Level 1 Gross Weight	3 kg
Package Level 1 Units	1 piece
Part Type	New
Product Name	Unclassified

Product Net Weight	3 kg
Product Type	Unclassified
Quote Only	No
Selling Unit of Measure	piece
Stocked At (Warehouses)	Wickliffe, Ohio, United States Malmö, Sweden
Technical Information	MPS 022 Power supply,AC/DC switched mode regulators for VMEbus applications Mains voltage 90-264 VAC and 130-350 VDC Main frequency 47-63 Hz Output voltage 5V, +12V, -12V Output Current 23A, 3,5A , 2A Dimmension Height 6U Dimmension Widht 12HP
UNSPSC	39120000
WEEE Category	Product Not in WEEE Scope

Categories

- Measurement and Analytics → Force Measurement → Stressometer 6.0 FSA
- Measurement and Analytics → Force Measurement → Stressometer 6.0 FSA → Flatness Systems → Flatness Measurement Systems
- Measurement and Analytics → Force Measurement → Stressometer 7.0 FSA
- Measurement and Analytics → Force Measurement → Stressometer 7.1 FSA → Flatness Systems → Flatness Measurement Systems
- Measurement and Analytics → Force Measurement → Stressometer 7.1 FSA
- Measurement and Analytics → Force Measurement → Stressometer 8.0 FSA → Flatness Systems → Flatness Measurement Systems
- Measurement and Analytics → Force Measurement → Stressometer 8.0 FSA
- Measurement and Analytics → Force Measurement → Stressometer 8.1 FSA

