


PRODUCT-DETAILS

# 3GAA061311-JSF

## IE2 High Efficiency Aluminum Motors, 0.18 kW, 400 V (3GAA061311-JSF)



General Information	
Product ID	3GAA061311-JSF
ABB Type Designation	M3AA 63A 2
Catalog Description	IE2 High Efficiency Aluminum Motors, 0.18 kW, 400 V (3GAA061311-JSF)

Ordering	
ABB Type Designation	M3AA 63A 2
Invoice Description	M3AA 63A 2
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015100
Replaced Product ID (OLD)	3GAA061001-JSE 3GVA061001-JSC 3GAA061001-JSC
Medium Description	0.18kW, 2 Poles, Frame Size 63, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB34/IM2101 Mounting (3GAA061311-JSF)

Short Description

0.18kW, 2P, Frame Size 63, 3PH, 400V, 50Hz, IP55, IMB34/IM2101

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	0.18 kW	2790 r/min	0.51 A	0.750	60.40 %	0.61 N·m	4.50
D	--	50 Hz	230 V	0.18 kW	2790 r/min	0.88 A	0.750	60.40 %	0.61 N·m	4.50
Y	--	60 Hz	460 V	0.18 kW	3420 r/min	0.46 A	0.700	64.00 %	0.50 N·m	5.30

Connection Configuration	Y
Temperature Class Default	--
Input Voltage (U <sub>in</sub> )	400 V
Frequency (f)	50 Hz
Output Power	0.18 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 60.4 % Partial Load (75%) 57.8 % Partial Load (50%) 49.5 %
IE Class Data (60 Hz)	IE Class IE2 Full Load (100%) 64.0 % Partial Load (75%) 60.2 % Partial Load (50%) 51.4 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	2
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Aluminum
Frame Size	63
Bearing	6201-2Z/C3
Bearing NDE	6201-2Z/C3
IM Class	IMB34 IM2101
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	208 mm
Product Net Height	154 mm

Product Net Width	124 mm
Product Net Weight	3.7 kg
Gross Weight	4.7 kg

**Classifications**

UNSPSC	26101100
--------	----------

**Categories**

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

