



PRODUCT-DETAILS

3GAA072062-ADA  
M1AA 71B 4

General Information	
Product ID	3GAA072062-ADA
ABB Type Designation	M1AA 71B 4
Catalog Description	M1AA 71B 4

Additional Information	
ABB Type Designation	M1AA 71B 4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6202-2Z/C3
Bearing NDE	6202-2Z/C3
Country of Origin	Türkiye (TR)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	400 V	0.37 kW	1390 r/min	1.15 A	0.690
Y	--	50 Hz	690 V	0.37 kW	1390 r/min	0.66 A	0.690
D	--	60 Hz	460 V	0.37 kW	1675 r/min	1.02 A	0.640

Frame Material	Aluminum
Frame Size	71
Gross Weight	0 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class NA Full Load (100%) 66.9 % Partial Load (75%) 66.1 % Partial Load (50%) 61.2 %
IE Class Data (60 Hz)	IE Class NA Full Load (100%) 71.2 % Partial Load (75%) 70.4 % Partial Load (50%) 65.3 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
Invoice Description	M1AA 71B 4
IP Class	IP55

Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	4
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	0 kg
Product Type	1AA1__M1AA_IE1_AA
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)