




PRODUCT-DETAILS

3GAA072311-BDE

IE2 High Efficiency Aluminum Motors, 0.25 kW,
400 V (3GAA072311-BDE)



General Information

Product ID	3GAA072311-BDE
ABB Type Designation	M3AA 71A 4
Catalog Description	IE2 High Efficiency Aluminum Motors, 0.25 kW, 400 V (3GAA072311-BDE)

Ordering

ABB Type Designation	M3AA 71A 4
Invoice Description	M3AA 71A 4
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Italy (IT) China (CN) Romania (RO)
Customs Tariff Number	85015100
Stocked At (Warehouses)	Menden, Germany
Medium Description	0.25kW, 4 Poles, Frame Size 71, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB5/IM3001 Mounting (3GAA072311-BDE)
Short Description	0.25kW, 4P, Frame Size 71, 3PH, 400V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data											
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	
D	--	50 Hz	400 V	0.25 kW	1430 r/min	0.76 A	0.670	68.50 %	1.67 N·m	4.70	
D	--	60 Hz	460 V	0.25 kW	1743 r/min	0.70 A	0.610	70.00 %	1.39 N·m	5.40	
Connection Configuration											D
Temperature Class Default											--
Input Voltage (U _{in})											400 V
Frequency (f)											50 Hz
Output Power											0.25 kW
Altitude											1000 m
Ambient Temperature											40 °C
IC Class											IC411
IE Class Data (50 Hz)											IE Class IE2 Full Load (100%) 68.5 % Partial Load (75%) 66.8 % Partial Load (50%) 59.9 %
IE Class Data (60 Hz)											IE Class IE2 Full Load (100%) 70.0 % Partial Load (75%) 67.4 % Partial Load (50%) 60.1 %
IP Class											IP55
Insulation Class											ICLF
Direction of Rotation											Both sides
Number of Poles (High)											4
Two Speed Motor											No
Type of Duty											S1
Voltage Code											D

Mechanical

Frame Material	Aluminum
Frame Size	71
Bearing	6203-2Z/C3
Bearing NDE	6202-2Z/C3
Lubrication	For life
IM Class	IMB5 IM3001
Terminator Box Location	Top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	239.5 mm
Product Net Height	180 mm
Product Net Width	136 mm
Product Net Weight	5.2 kg
Gross Weight	8.2 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

Standards	IEC 60034-1
UNSPSC	26101100

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

