




PRODUCT-DETAILS

3GAA082314-ADE

IE2 High Efficiency Aluminum Motors, 0.75 kW,
400 V (3GAA082314-ADE)



General Information

Product ID	3GAA082314-ADE
ABB Type Designation	M3AA 80D 4
Catalog Description	IE2 High Efficiency Aluminum Motors, 0.75 kW, 400 V (3GAA082314-ADE)

Ordering

ABB Type Designation	M3AA 80D 4
Invoice Description	M3AA 80D 4
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Italy (IT) China (CN) Romania (RO)
Customs Tariff Number	85015100
Stocked At (Warehouses)	Menden, Germany
Medium Description	0.75kW, 4 Poles, Frame Size 80, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GAA082314-ADE)
Short Description	0.75kW, 4P, Frame Size 80, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	400 V	0.75 kW	1415 r/min	1.65 A	0.820	79.80 %	5.00 N·m	5.90
D	--	60 Hz	460 V	0.75 kW	1730 r/min	1.62 A	0.700	82.60 %	4.10 N·m	7.00
Connection Configuration										D
Temperature Class Default										--
Input Voltage (U _{in})										400 V
Frequency (f)										50 Hz
Output Power										0.75 kW
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE2
										Full Load (100%) 79.8 %
										Partial Load (75%) 81.3 %
										Partial Load (50%) 79.9 %
IE Class Data (60 Hz)										IE Class IE2
										Full Load (100%) 82.6 %
										Partial Load (75%) 82.5 %
										Partial Load (50%) 79.8 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										4
Two Speed Motor										No
Type of Duty										S1
Voltage Code										D

Mechanical

Frame Material	Aluminum
Frame Size	80
Bearing	6204-2Z/C3
Bearing NDE	6203-2Z/C3
Lubrication	For life
IM Class	IMB3 IM1001
Terminator Box Location	Top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	292.5 mm
Product Net Height	193.5 mm
Product Net Width	154 mm
Product Net Weight	10 kg
Gross Weight	13 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

Standards	IEC 60034-1
UNSPSC	26101100

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

