


PRODUCT-DETAILS

# 3GAA082314-JSE

## IE2 High Efficiency Aluminum Motors, 0.75 kW, 400 V (3GAA082314-JSE)



General Information	
Product ID	3GAA082314-JSE
ABB Type Designation	M3AA 80D 4
Catalog Description	IE2 High Efficiency Aluminum Motors, 0.75 kW, 400 V (3GAA082314-JSE)

Ordering	
ABB Type Designation	M3AA 80D 4
Invoice Description	M3AA 80D 4
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Italy (IT) Romania (RO)
Customs Tariff Number	85015100
Medium Description	0.75kW, 4 Poles, Frame Size 80, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB34/IM2101 Mounting (3GAA082314-JSE)
Short Description	0.75kW, 4P, Frame Size 80, 3PH, 400V, 50Hz, IP55, IMB34/IM2101

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Torque
D	--	50 Hz	230 V	0.75 kW	1415 r/min	2.80 A	0.820	5.00 N·m
Y	--	50 Hz	400 V	0.75 kW	1415 r/min	1.65 A	0.820	5.00 N·m
Y	--	60 Hz	460 V	0.75 kW	1730 r/min	1.62 A	0.700	4.10 N·m

Connection Configuration	Y
Temperature Class Default	--
Input Voltage (U <sub>in</sub> )	400 V
Frequency (f)	50 Hz
Output Power	0.75 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 79.8 % Partial Load (75%) 81.3 % Partial Load (50%) 79.9 %
IE Class Data (60 Hz)	IE Class IE2 Full Load (100%) 82.6 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	4
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Aluminum
Frame Size	80
Bearing	6204-2ZC3
Bearing NDE	6203-2ZC3
Lubrication	For life
IM Class	IMB34 IM2101
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	292.5 mm
Product Net Height	193.5 mm
Product Net Width	154 mm
Product Net Weight	12 kg
Gross Weight	12.5 kg

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications	
Standards	IEC 60034-1
UNSPSC	26101100

Categories
Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

