



PRODUCT-DETAILS

3GAA083310-ASP
QAL 132SA 6

General Information

Product ID	3GAA083310-ASP
ABB Type Designation	QAL 80MA 6
Catalog Description	QAL 132SA 6

Ordering

ABB Type Designation	QAL 80MA 6
Invoice Description	QAL 132SA 6
Product Name	3-Phase squirrel cage motor
Product Type	QAL
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015100

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque
Y	--	50 Hz	380 V	0.37 kW	940 r/min	1.09 A	0.700	73.50 %	3.76 N·m

Temperature Class	--
Default	
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	6
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical	
Frame Material	Aluminum
Frame Size	80
Bearing	6204-2Z/C3
Bearing NDE	6204-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions	
Package Level 1 Units	0 carton
Product Net Weight	8.5 kg
Gross Weight	11.5 kg

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Classifications	
UNSPSC	26101100

Categories	
Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE3 Premium Efficiency Aluminum Motors	