


PRODUCT-DETAILS

3GAA081313-JSE

IE2 High Efficiency Aluminum Motors, 1.1 kW, 400 V (3GAA081313-JSE)



General Information	
Product ID	3GAA081313-JSE
ABB Type Designation	M3AA 80C 2
Catalog Description	IE2 High Efficiency Aluminum Motors, 1.1 kW, 400 V (3GAA081313-JSE)

Ordering	
ABB Type Designation	M3AA 80C 2
Invoice Description	M3AA 80C 2
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Poland (PL) Finland (FI) China (CN) Romania (RO)
Customs Tariff Number	85015220
Stocked At (Warehouses)	Menden, Germany Vittuone, Italy

Medium Description	1.1kW, 2 Poles, Frame Size 80, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB34/IM2101 Mounting (3GAA081313-JSE)
Short Description	1.1kW, 2P, Frame Size 80, 3PH, 400V, 50Hz, IP55, IMB34/IM2101

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	1.10 kW	2875 r/min	2.40 A	0.800	79.60 %	3.60 N·m	7.80
D	--	50 Hz	230 V	1.10 kW	2870 r/min	4.10 A	0.800	79.60 %	3.60 N·m	7.80
Y	--	60 Hz	460 V	1.10 kW	3490 r/min	2.10 A	0.780	82.60 %	3.00 N·m	9.10

Connection Configuration	Y
Temperature Class Default	--
Input Voltage (U _{in})	400 V
Frequency (f)	50 Hz
Output Power	1.1 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 79.6 % Partial Load (75%) 79.3 % Partial Load (50%) 76.7 %
IE Class Data (60 Hz)	IE Class IE2 Full Load (100%) 82.6 % Partial Load (75%) 81.9 % Partial Load (50%) 78.7 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	2
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Aluminum
Frame Size	80
Bearing	6204-2Z/C3
Bearing NDE	6203-2Z/C3
Lubrication	For life
IM Class	IMB34 IM2101
Terminator Box Location	Top

Dimensions

Package Level 1 Units	0 carton
-----------------------	----------

Product Net Depth / Length	292.5 mm
Product Net Height	193.5 mm
Product Net Width	154 mm
Product Net Weight	11 kg
Gross Weight	14 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

Standards	IEC 60034-1
UNSPSC	26101100

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

