



PRODUCT-DETAILS

3GAA082350-ASK

IE3 Premium Efficiency Aluminum Motors, 0.75 kW, 400 V (3GAA082350-ASK)



General Information

Product ID	3GAA082350-ASK
ABB Type Designation	M3AA 80ME 4
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 0.75 kW, 400 V (3GAA082350-ASK)

Ordering

ABB Type Designation	M3AA 80ME 4
Invoice Description	M3AA 80ME 4
Product Name	3-Phase squirrel cage motor
Product Type	3AA3_M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN) Finland (FI) Romania (RO) Poland (PL)
Customs Tariff Number	85015100
Stocked At (Warehouses)	Menden, Germany Sant Quirze del Vallés - BCN, Spain Vittuone, Italy
Medium Description	0.75kW, 4 Poles, Frame Size 80, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GAA082350-ASK)

Short Description0.75kW, 4P, Frame Size 80, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	0.75 kW	1440 r/min	1.68 A	0.760	82.60 %	4.90 N·m	7.90
D	--	50 Hz	230 V	0.75 kW	1440 r/min	2.92 A	0.760	82.50 %	4.90 N·m	7.90
Y	--	50 Hz	380 V	0.75 kW	1431 r/min	1.70 A	0.800	82.50 %	5.00 N·m	7.40
D	--	50 Hz	220 V	0.75 kW	1431 r/min	2.93 A	0.800	82.50 %	5.00 N·m	7.40
Y	--	50 Hz	415 V	0.75 kW	1445 r/min	1.67 A	0.740	82.50 %	4.90 N·m	8.30
Y	--	60 Hz	460 V	0.75 kW	1748 r/min	1.48 A	0.740	85.50 %	4.00 N·m	9.50

Connection Configuration	Y
Temperature Class Default	--
Input Voltage (U _{in})	400 V
Frequency (f)	50 Hz
Output Power	0.75 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 82.5 % Partial Load (75%) 82.1 % Partial Load (50%) 79.4 %
IE Class Data (60 Hz)	IE Class IE4 Full Load (100%) 85.5 % Partial Load (75%) 84.4 % Partial Load (50%) 81.6 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	4
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Aluminum
Frame Size	80
Bearing	6204-2Z/C3
Bearing NDE	6203-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	293.5 mm
Product Net Height	193.5 mm
Product Net Width	149.5 mm
Product Net Weight	13.5 kg
Gross Weight	16.5 kg

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications	
UNSPSC	26101100

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

