




PRODUCT-DETAILS

3GAA083311-BSE

IE2 High Efficiency Aluminum Motors, 0.37 kW,
400 V (3GAA083311-BSE)



General Information

Product ID	3GAA083311-BSE
ABB Type Designation	M3AA 80A 6
Catalog Description	IE2 High Efficiency Aluminum Motors, 0.37 kW, 400 V (3GAA083311-BSE)

Ordering

ABB Type Designation	M3AA 80A 6
Invoice Description	M3AA 80A 6
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN) Romania (RO)
Customs Tariff Number	85015100
Stocked At (Warehouses)	Menden, Germany Sant Quirze del Vallés - BCN, Spain Shanghai, China Vittuone, Italy
Medium Description	0.37kW, 6 Poles, Frame Size 80, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB5/IM3001 Mounting (3GAA083311-BSE)
Short Description	0.37kW, 6P, Frame Size 80, 3PH, 400V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	0.37 kW	923 r/min	1.04 A	0.730	67.60 %	3.82 N·m	4.40
D	--	50 Hz	230 V	0.37 kW	923 r/min	1.79 A	0.730	67.60 %	3.82 N·m	4.40
Y	--	60 Hz	460 V	0.37 kW	1136 r/min	0.93 A	0.680	64.00 %	3.11 N·m	5.10

Connection Configuration	Y
Temperature Class	--
Default	
Input Voltage (U _{in})	400 V
Frequency (f)	50 Hz
Output Power	0.37 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 67.6 % Partial Load (75%) 67.5 % Partial Load (50%) 62.6 %
IE Class Data (60 Hz)	IE Class IE2 Full Load (100%) 64.0 % Partial Load (75%) 62.0 % Partial Load (50%) 54.9 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	6
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Aluminum
Frame Size	80
Bearing	6204-2Z/C3
Bearing NDE	6203-2Z/C3
Lubrication	For life
IM Class	IMB5 IM3001
Terminator Box Location	Top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	292.5 mm
Product Net Height	193.5 mm
Product Net Width	154 mm
Product Net Weight	9 kg
Gross Weight	12 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

SCIP27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

Standards	IEC 60034-1
UNSPSC	26101100

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

