



PRODUCT-DETAILS

3GAA091442-AHE

No Description Available

"No longer for sale" replaced by 3GAA091500-

General Information	
Product ID	3GAA091442-AHE
ABB Type Designation	M3AA 90L 2
EAN	3GAA091442-AHE
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M3AA 90L 2
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6205-2Z/C3
Bearing NDE	6204-2Z/C3
Country of Origin	Spain (ES) China (CN) Sweden (SE)
Customs Tariff Number	85015220
Direction of Rotation	Both sides
EAN	3GAA091442-AHE

Electrical Data							
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	415 V	1.50 kW	2910 r/min	2.90 A	0.840

Frame Size	90
Gross Weight	16.48 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 84.1 % Partial Load (75%) 84.3 % Partial Load (50%) 82.2 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	2
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor

Product Net Weight	16 kg
Product Type	3AA2_M3AA_IE2_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA091500-AHE
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	H