



PRODUCT-DETAILS

3GAA092444-BGE

No Description Available

"No longer for sale" replaced by 3GAA092520-

General Information								
Product ID	3GAA092444-BGE							
ABB Type Designation	M3AA 90LB 4							
EAN	3GAA092444-BGE							
Catalog Description	No Description Available							
Additional Information								
ABB Type Designation	M3AA 90LB 4							
Altitude	1000 m							
Ambient Temperature	40 °C							
Bearing	6205-2Z/C3							
Bearing NDE	6204-2Z/C3							
Country of Origin	Spain (ES) China (CN) Sweden (SE)							
Customs Tariff Number	85015220							
Direction of Rotation	Both sides							
EAN	3GAA092444-BGE							
Electrical Data								
	Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
	Y	--	50 Hz	415 V	1.10 kW	1440 r/min	2.30 A	0.780
Frame Size	90							
Gross Weight	16.48 kg							
IC Class	IC411							
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 83.2 % Partial Load (75%) 83.1 % Partial Load (50%) 81.0 %							
IM Class	IMB5 IM3001							
Insulation Class	ICLF							
IP Class	IP55							
Lubrication	For life							
Made To Order	No							
Minimum Order Quantity	1 piece							
Number of Poles (High)	4							
Order Multiple	1 piece							
Package Level 1 Units	0 carton							
Product Name	3-Phase squirrel cage motor							

Product Net Weight	16 kg
Product Type	3AA2_M3AA_IE2_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA092520-BGE
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	G