




PRODUCT-DETAILS

3GAA092315-BSE

IE2 High Efficiency Aluminum Motors, 1.5 kW, 400 V (3GAA092315-BSE)



General Information

Product ID	3GAA092315-BSE
ABB Type Designation	M3AA 90LD 4
Catalog Description	IE2 High Efficiency Aluminum Motors, 1.5 kW, 400 V (3GAA092315-BSE)

Ordering

ABB Type Designation	M3AA 90LD 4
Invoice Description	M3AA 90LD 4
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Poland (PL) China (CN) Sweden (SE)
Customs Tariff Number	85015220
Medium Description	1.5kW, 4 Poles, Frame Size 90, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB5/IM3001 Mounting (3GAA092315-BSE)
Short Description	1.5kW, 4P, Frame Size 90, 3PH, 400V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data										
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	230 V	1.50 kW	1435 r/min	5.70 A	0.760	84.20 %	9.90 N·m	7.00
Y	--	50 Hz	400 V	1.50 kW	1435 r/min	3.30 A	0.760	84.20 %	9.90 N·m	7.00
Y	--	60 Hz	460 V	1.50 kW	1750 r/min	3.00 A	0.720	84.90 %	8.10 N·m	8.20
Connection Configuration										Y
Temperature Class Default										--
Input Voltage (U _{in})										400 V
Frequency (f)										50 Hz
Output Power										1.5 kW
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE2
										Full Load (100%) 84.2 %
										Partial Load (75%) 84.1 %
										Partial Load (50%) 81.9 %
IE Class Data (60 Hz)										IE Class IE2
										Full Load (100%) 84.9 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										4
Two Speed Motor										No
Type of Duty										S1
Voltage Code										S

Mechanical

Frame Material	Aluminum
Frame Size	90
Bearing	6205-2Z/C3
Bearing NDE	6204-2Z/C3
Lubrication	For life
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	331.5 mm
Product Net Height	217 mm
Product Net Width	177 mm
Product Net Weight	16 kg
Gross Weight	16.48 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications	
Standards	IEC 60034-1
UNSPSC	26101100

Categories
Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

