



PRODUCT-DETAILS

3GAA092445-BGE

No Description Available

"No longer for sale" replaced by 3GAA092540-

General Information	
Product ID	3GAA092445-BGE
ABB Type Designation	M3AA 90LD 4
EAN	3GAA092445-BGE
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M3AA 90LD 4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6205-2Z/C3
Bearing NDE	6204-2Z/C3
Country of Origin	Spain (ES) China (CN) Sweden (SE)
Customs Tariff Number	85015220
Direction of Rotation	Both sides
EAN	3GAA092445-BGE
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
Y	--	50 Hz	415 V	1.50 kW	1445 r/min	3.30 A	0.750

Frame Size	90
Gross Weight	20.48 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 83.9 % Partial Load (75%) 83.3 % Partial Load (50%) 80.4 %
IM Class	IMB5 IM3001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	4

Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	20 kg
Product Type	3AA2__M3AA_IE2_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA092540-BGE
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	G